





DIMENSIONS TABLE						
CATALOG NUMBER	AA	BB	CC	FF	GG	NO. OF POSITIONS
RPIG48U__VR__	2,349 59,67	2,140 54,36	1,742 44,25	1,500 38,10	1,955 49,66	48
RPIG72U__VR__	3,149 79,98	2,940 74,68	2,542 64,57	2,300 58,42	2,755 69,98	72
RPIG96U__VR__	3,949 100,30	3,740 95,00	3,342 84,89	3,100 78,74	3,555 90,30	96
RPIG120U__VR__	4,749 120,62	4,540 115,32	4,412 105,21	3,900 99,06	4,355 110,62	120
RPIG150U__VR__	5,749 146,02	5,540 140,72	5,142 130,61	4,900 124,46	5,355 136,02	150

TAIL LENGTH TABLE	
CATALOG NUMBER	DD ±0,15 ±0,38
RPIG__U__VR__-1	.108 2,74
RPIG__U__VR__-2	.172 4,37
RPIG__U__VR__-3	.108 2,74
RPIG__U__VR__-4	.172 4,37

TYPICAL CATALOG NUMBER DESIGNATION



NOTES: UNLESS OTHERWISE SPECIFIED;

MATERIALS:

BODY: GLASS REINFORCED POLYESTER UL94-0; COLOR-BLACK.

CONTACTS: COPPER ALLOY

CONTACT FINISH:

B: 30 MICROINCHES [0,76 MICRONS] MIN GOLD IN CONTACT AREA AND 200 MICROINCHES [5,08 MICRONS] MIN TIN/LEAD ALLOY ON CONTACT TAILS. 50 MICROINCHES [1,27 MICRONS] MIN NICKEL UNDERPLATE ALL OVER.

D: 5 MICROINCHES [0,13 MICRONS] MIN GOLD OVER 30 MICROINCHES [0,76 MICRONS] MIN PALLADIUM NICKEL IN CONTACT AREA AND 100 MICROINCHES [2,54 MICRONS] MIN TIN/LEAD ALLOY ON CONTACT TAILS. 50 MICROINCHES [1,27 MICRONS] MIN NICKEL UNDERPLATE ALL OVER.

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	projection INCH/MM	product family DIN		
ltr	ecn	no	dr	date	tolerances unless otherwise specified			title		
1	ECN3590	RPS	10/01/96		angles	.XX±.01/.3	INCH/MM	GUIDED DIN VERTICAL RECEPTACLE		
2	ECN3717	DAF	5/21/97		linear	.XXX±.005/.13		dwg no		
D	V20210	TAB	2/30/02	0°±2'		.XXXX±.0020/.051	scale 2:1	sheet 1 of 1 size		
E	M06-0330	AGS	8/25/06	dr	DLB	11/18/91		SE94743		
				enr	JAM	11/25/91		A3		
				chr	SFC	12/30/91		type		
				appd	TK	12/30/91		Product Customer Drawing		
sheet index	revision	E								
	sheet	1								