

C3225X7R2J473K200AA (TDK item description : C3225X7R2J473KT****)

Applications



Commercial Grade



Please refer to Part No. CGA6M4X7R2J473K200AA for automotive use.


Feature

Mid

Mid Voltage (100 to 630V)

Series

C3225 [EIA CC1210]



Size

Length(L)	3.20mm +/-0.40mm
Width(W)	2.50mm +/-0.30mm
Thickness(T)	2.00mm +/-0.20mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	
Recommended Land Pattern(PA)	2.00 to 2.40mm
Recommended Land Pattern(PB)	1.00 to 1.20mm
Recommended Land Pattern(PC)	1.90 to 2.50mm
Recommended Slit Pattern(SD)	

Electrical Characteristics


Capacitance	47nF +/-10%
Rated Voltage	630Vdc
Temperature Characteristic	X7R(+/-15%)
Dissipation Factor	3% Max.
Insulation Resistance	10000MΩ Min.

Other


Soldering Method	Reflow
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	1000Pcs Min.

C3225X7R2J473K200AA


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




C3225X7R2J473K200AA




C3225X7R2J473K200AA




C3225X7R2J473K200AA



C3225X7R2J473K200AA



C3225X7R2J473K200AA(DC Bias = 0V) C3225X7R2J473K200AA(DC Bias = 315V)



C3225X7R2J473K200AA(100kHz)

C3225X7R2J473K200AA(500kHz)

C3225X7R2J473K200AA(1MHz)