



LOC		DIST		REVISONS			
FX	00	P	LYR	DESCRIPTION	DATE	DWN	APVD
		B		REVISED PER ECO-09-009390	16APR2009	DD	RB
		C		REVISED PER ECO-11-017736	30SEP2011	DD	RB


- ⚠ BACKSHELL IS NOT CURRENTLY TOOLED FOR PRODUCTION.
2. ELBOW DESIGN ALLOWS FOR 360° EXIT ROTATION.
- ⚠ DIMENSION TO BE MEASURED WHEN THE COVER IS CLOSED.




2035048-1
SCALE 3:1




2035048-5
SCALE 3:1




2035048-2
SCALE 3:1





2035048-6
SCALE 3:1



2035048-3
SCALE 3:1



2035048-7
SCALE 3:1



TE PART NUMBER	ASSY POSN	NOMINAL CONDUIT SIZE		NOMINAL DIMENSIONS			
		NC	NW	C	D	(E)	H
2035048-1	2	08	7.5	23.9	18.3	48.3	7.8
2035048-2	3	08	7.5	28.5	18.3	48.3	7.8
2035048-3	4	08	7.5	29.1	23.6	52.3	7.8
2035048-4	6	⚠ NOT CURRENTLY TOOLED					
2035048-5	2	12	10	23.9	18.3	48.3	11.0
2035048-6	3	12	10	28.5	18.3	48.3	11.0
2035048-7	4	12	10	29.1	23.6	52.3	11.0
2035048-8	6	⚠ NOT CURRENTLY TOOLED					
2035048-9	8	⚠ NOT CURRENTLY TOOLED					

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MARKEY 28MAR2008	TE Connectivity	
DIMENSIONS:		CHK J. MARKEY 28MAR2008		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. MARKEY 28MAR2008	NAME BACKSHELL, AMPSEAL 16, 90 DEGREE EXIT	
	9 PLC ±.5	PRODUCT SPEC	SIZE CAGE CODE DRAWING NO A100779C-2035048	
	1 PLC ±.5	APPLICATION SPEC		
MATERIAL	FINISH	WEIGHT	RESTRICTED TO	
NYLON 6/6	-	-	A100779C-2035048	
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1 REV C