





Dimensions shown are IEC/ANSI standards

Nominal Voltage:	1.5 V
Operating Voltage	1.6 - 0.75V
Impedance:	150 m-ohm @ 1kHz
Typical Weight:	69 gm (2.4 oz.)
Typical Volume:	26.9 cm ³ (1.6 in. ³)
Terminals:	Flat
Storage Temperature Range:	-20 ⁰ C to 35 ⁰ C
Operating Temperature Range:	-20 ⁰ C to 54 ⁰ C (-4 ⁰ F to 130 ⁰ F)
ANSI: IEC:	14A LR14

DURACELL[®]


BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
Internet: www.duracell.com




* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.


TYPICAL DISCHARGE CHARACTERISTICS
AT 21°C (70°F)




TYPICAL DISCHARGE CHARACTERISTICS
AT 21°C (70°F)




TYPICAL DISCHARGE CHARACTERISTICS
AT 21°C (70°F)



TYPICAL DISCHARGE CHARACTERISTICS
AT 21°C (70°F)



TYPICAL FLASHLIGHT TEST
AT 21°C AND 0°C



DURACELL®
BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
Internet: www.duracell.com

* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Duracell:](#)

[MN1400](#)