

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION





19

© COPYRIGHT 19

BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS

RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION		
L			L	REVISED; ECN AA-6527	11-90	LHS NJ



- 1 MATERIAL: HOUSING - PBT POLYESTER, BLACK, TERMINAL - .0138 THICK PHOS-BRONZE PLATED WITH .00005 THICK HARD GOLD IN LOCALIZED GOLD PLATE AREA AND .00008 THICK TIN-LEAD IN SOLDER AREA OVER .00005 THICK NICKEL UNDERPLATE.
- 2 CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68 AND REA BULLETIN 345-81, PE-76 SPECIFICATION FOR MODULAR TELEPHONE HARDWARE.
3. FOR APPLICATION INFORMATION SEE AMP SPECIFICATION 114-2048.
4. FOR PERFORMANCE REQUIREMENTS SEE AMP SPECIFICATION 108-1163.
5. ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 6 VENDOR DESIGNATION SHALL BE THE LETTER 'A' ON THIS SURFACE.
- 7 BULK PACKAGED IN A TRAY.
- 8 PACKAGED 28 PER TUBE.

6	6	-4
6	6	-3
4	4	520258 - 2
PACKAGED	CONTACTS	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± ANGLES ±	CONTRACT NO DR <i>STWARTEN 12/2/87</i> CHK <i>A.C. Clark 12-4-87</i> APPD <i>[Signature] 12/4/87</i> APPD <i>[Signature] 12-4-87</i> DSGN APPD OTHER APPD	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
MATERIAL 1	NAME PRINTED CIRCUIT BOARD MODULAR JACK ASSEMBLY, TOP ENTRY, 6 POSITION, FLANGELESS WITH PANEL STOPS	SIZE C	FSCM NO 00779
FINISH 1		DRAWING NO 520258	SCALE 4:1
			SHEET 1 of 1