

426MHz THROUGH-HOLE SAW FILTER

AFS426.0W01-TD01



RoHS
Compliant



11.3 x 4.8 x 3.5 mm

FEATURES:

- Compact size resistance weld sealed package
- No polarity

APPLICATIONS:

- Pager (Double Super)

STANDARD SPECIFICATIONS:


MAXIMUM RATINGS

Item	Value
Operation Temperature Range	-40°C to +80°C
Storage Temperature Range	-40°C to +85°C
DC Permissive Voltage	10V DC max.
Maximum Input Power	+0 dBm

ELECTRICAL CHARACTERISTICS

Item	Frequency (MHz)	Specification
Center Frequency (f_o)	426.0	
Pass Band Width	$f_o \pm 2.0$	
Insertion Loss	Pass Band	4.5 dB max
Ripple Deviation	Pass Band	2.0 dB max.
Stop Band Suppression	$f_o - 100 \sim f_o - 40.8$ $f_o + 40.8 \sim f_o + 100$	55 dB min. 55 dB min.
Terminating Impedance		150Ω/0pF

TEST CIRCUIT



426MHz THROUGH-HOLE SAW FILTER

AFS426.0W01-TD01





RoHS
Compliant




11.3 x 4.8 x 3.5 mm

FREQUENCY CHARACTERISTICS:



OUTLINE DIMENSIONS:



Pin No.	Function
Pin 1	Input
Pin 4	Output
Pin 2, 3	Ground

Dimension : mm

NOTE: Abracon manufactured products are intended for general commercial and industrial use. For applications requiring high reliability and/or presenting extreme operating environment, written consent & authorization from Abracon is required.