




- 1 MATERIAL
HOUSING: GLASS FILLED HIGH TEMPERATURE NYLON.
CONTACT: PHOS. BRONZE, C51100, TEMPER H06.
- 2 FINISH
CONTACT:
NICKEL PLATE ALL OVER .00127mm - .0019mm [0.00050 IN -.00075 IN] THK.
PER AMP SPEC 112-25-2.
3. GOLD PLATE IN INTERFACE AREA .00038mm [0.00015 IN] THK.
PER AMP SPEC 112-162-5.
MATTE TIN PLATE IN SOLDER TAIL AREA .00381mm - .00635mm [0.00150 IN -.00250 IN] THK.
PER AMP SPEC 112-65-1.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	3.60 [1.42]	2.54±0.05 [1.00±.002]	DETAIL-C	DETAIL-A	NON-BUFFERED DRAM, 3.3 VOLT, PRE-PLATED CONTACTS	5390213-3
OBSOLETE	2.59 [1.02]	2.54±0.05 [1.00±.002]	DETAIL-B	DETAIL-A	SYNC DRAM, 3.3 VOLT, PRE-PLATED CONTACTS	5390213-2
	2.59 [1.02]	2.54±0.05 [1.00±.002]	DETAIL-C	DETAIL-A	NON-BUFFERED DRAM, 3.3 VOLT, PRE-PLATED CONTACTS	5390213-1
	DIM B	DIM A	KEY #1	KEY #2	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. RICHARDSON CHK M. YEOMANS APVD	R0EC04 R0EC04	Tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127 [0.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
MATERIAL 1		FINISH 2		WEIGHT CUSTOMER DRAWING	
				A100779C=5390213	
				SCALE 1:1 SHEET 1 OF 2 REV B2	

