




VERSION WITHOUT RIBS



NOTES :

1- MATERIAL:

-HOUSING: LCP FIBER GLASS FILLED 94-V-0 COLOR BLACK.

-TERMINAL: COPPER ALLOY PLATED WITH:

BASE FINISH: NICKEL

CONTACT SURFACE FINISH:

GOLD

OR

GOLD FLASH OVER PALLADIUM NICKEL

EXCEEDS PRODUCT REQUIREMENTS BASED ON PS-95522-002

2- PC BOARD THICKNESS : 1.57

3- JACK FOR MATING WITH IEC 60603-7 AND TIA-1096-A PLUGS
90075 MOLEX SERIES .

4- PRODUCT SPECIFICATION PS-95522-002.


5- APPLICATION SPECIFICATION AS-85513-001

6- PACKAGING SPECIFICATION PK-95022. (SHT.1 TRAY PACKAGING)
PK-95022. (SHT.2 TUBE PACKAGING)

7- FOR ILLUSTRATION PURPOSES A 4 CIRCUIT IS SHOWN.

8- MANUFACTURING I.D. CAN BE EITHER MG, MXF OR MXI.

LAST INSPECTION NUMBER: 19




CORRECTED PRODUCT SPEC		QUALITY SYMBOLS	DESCRIPTION
EC NO:	REV		
IPG2013-0619	1	▽=0	
DRWN:DBYRNES	2	▽=0	
CHKD:MAHER	3		
APPR:STGRIFFIN	4		
REV			

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ± ---	± ---
3 PLACES ± ---	± ---
2 PLACES ± 0.25	± .014
1 PLACE ± 0.35	± ---
ANGULAR ± 2 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
mm ONLY	DATE
DRAWN BY	KNOLLER
CHECKED BY	FCARABET
APPROVED BY	KNOLLER
MATERIAL NO.	SEE CHART SHT. 2

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
1:1	METRIC	
HIGH PROFILE TOP ENTRY JACK		
MOLEX INCORPORATED		
DOCUMENT NO.	SD-95522-001	SHEET NO.
1 OF 2		



MOUNTING HOLE PATTERNS
(SEE FROM COMPONENT SIDE)
ALL DIMENSIONS REF DIMENSIONS

PART NUMBERS FOR JACK WITH RIBS										
	TYPE	PACKA- GING	POS. 4	TOOLED	POS. 6	TOOLED	POS. 6	TOOLED	POS. 8	TOOLED
			4 CKTS.		4 CKTS.		6 CKTS.		8 CKTS.	
			TRAY	95522-2447	X	95522-2647	X	95522-2667	X	95522-2887
		TUBE					95522-2617 SEE NOTE 8 SH.1	X		

PART NUMBERS FOR JACK WITHOUT RIBS										
	TYPE	PACKA- GING	POS. 4	TOOLED	POS. 6	TOOLED	POS. 6	TOOLED	POS. 8	TOOLED
			4 CKTS.		4 CKTS.		6 CKTS.		8 CKTS.	
		TRAY	95522-2441	X	95522-2641	X	95522-2661	X	95522-2881	
		TUBE					95522-2611	X	95522-2881	

DIM. \ TYPE	POS. 4	POS. 6		POS. 8
	4 CKTS.	4 CKTS.	6 CKTS.	8 CKTS.
A	11.18	13.21	13.21	15.24
B	7.62	10.16	10.16	11.43
C (WITH RIBS)	14.00	16.00	16.00	18.00
D	3.81	3.81	6.35	8.89
H	7.82	9.88	9.88	11.94
J	5.64	6.70	6.70	6.30
K	3.07	4.06	4.06	4.06

REMOVED PLATING OPTIONS

EC NO: IPG2012-0698

DRWN:DBYRNES

CHKD:MSHAHAN

APPR:EFOLAN

2012/04/02

2012/04/17

2012/06/28

DESCRIPTION

REV

QUALITY SYMBOLS

GENERAL TOLERANCES (UNLESS SPECIFIED)

DIMENSION STYLE

SCALE

DESIGN UNITS

THIRD ANGLE PROJECTION

HIGH PROFILE TOP ENTRY JACK

MOLEX INCORPORATED

SD-95522-001

2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION