

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION			DATE	APVD
					DWN	
	C	ECR-05-017969			14DEC05	JMS FWK

NOTES:

- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Au PLATING
- 4 Ni PLATING
- 5 THIS ITEM MUST BE WHITE

- 6 ELECTRICAL CHARACTERISTICS
- FREQUENCY RANGE:

NOMINAL IMPEDANCE:

INSULATION RESISTANCE:

WORKING VOLTAGE:

DIELECTRIC WITHSTAND VOLTAGE:

CONTACT RESISTANCE:

CENTRE CONTACT:

OUTER CONTACT:

VSWR @ xGHz:

INSERTION LOSS xdb:
- DC - 4 GHz

50 Ohm

5000 MOhm

500 Volts RMS at Sea Level

1500 Volts RMS Max

1.50 mOhm Max

0.20 mOhm Max

N/A

N/A

- 7 MECHANICAL CHARATERISTICS
- COUPLING RETENTION FORCE:


CABLE RETENETION FORCE:

DURABILITY:
- 445N Min

N/A


500 Cycles Min

- 8 ENVIRONMENTAL CHARACTERISTICS
- OPERATING TEMPERATURE:
- 65 to +165 DegC



		1	1	BRASS	4	CAP	16
		1	1	PTFE		INSULATION	15
		1	1	BRASS	3	CONTACT 3	14
		2	2	SRASS	3	CONTACT 2	13
		2	2	PTFE		INSULATION	12
		2	2	BRASS	4	SLEEVE	11
		2	2	BRASS	4	BODY 3	10
		1	1	BRASS	4	BODY 2	9
		1	1	BRASS	4	WASHER	8
		1	1	SPRING STEEL		SPRING	7
		1	1	BRASS	4	RETAINING RING	6
		1	1	SILICON RUBBER	5	GASKET	5
		1	1	BRASS	4	BODY 1	4
		1	1	BRASS	3	CONTACT 1	3
		1	1	PTFE		INSULATION	2
		1	1	BRASS	4	SHELL	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		4	4				

QUANTITY PER ASSY			PARTS LIST		
-------------------	--	--	------------	--	--

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL	14DEC05	tyco Electronics		Tyco Electronics Corporation	
		CHK S.PARLOW	14DEC05			Bideford EX39 4HE	
DIMENSIONS: mm		APVD F.WHEELER-KING		14DEC05		NAME	
		PRODUCT SPEC				BNC Y ADAPTOR P-J-J 50 OHM	
		—				—	
		APPLICATION SPEC				—	
MATERIAL		—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE TABLE		WEIGHT		A3	00779	C-1337460	—
CUSTOMER DRAWING				SCALE	NTS	SHEET	1 OF 1
						REV	C