




HERMAPHRODITIC BLADE AND RECEPTACLE CONNECTOR

Wire-to-Board, Board-to-Board and Dust Cover

HERMAPHRODITIC BLADE AND RECEPTACLE CONNECTOR

WIRE-TO-BOARD

The wire-to-board connector is a plug connector that mates to the latest part number series of the surface mount hermaphroditic blade and receptacle board to board connectors. The connector provides power to the first LED printed circuit board in a string of rigid printed circuit board light strips.

KEY FEATURES

- Available in 2, 4, and 6 positions
- Connector mates to hermaphroditic blade and receptacle board-to-board part numbers with latching feature
- Positive Latching
- Connector accepts crimp snap contacts
- Contacts accept 18 AWG – 22 AWG stranded wire
- Contacts packaged on 24 inch reels for high speed lead termination
- Housings are bulk packaged
- RoHS compliant
- Custom length wire-to-board cable assemblies are available upon request

APPLICATIONS

- LED Lighting Controls
- LED Lighting Strips
- Channel Lettering

ELECTRICAL

- Operating Current : 6 AMPS
- Operating Voltage : 125VAC/125VDC
- Dielectric Withstanding Voltage : 1500VAC

MECHANICAL

- Operating Temperature: -40°C to +105°C
- Mating cycles: 10

MATERIALS

- Housings: UL 94 V-0
- Contacts: Tin plated brass

STANDARDS & SPECIFICATIONS

- Wire-to-Board Application Specification: [114-13252](#)
- Wire-to-Board Product Specification: [108-2387](#)
- UL and cUL recognized : File No. E28476

APPLICATION TOOLING

- PRO-CRIMPER III Hand Tool (includes die set): [2063778-1](#)
- Die Set for Hand Tool: [2063778-2](#)

For more information visit: tooling.te.com

HERMAPHRODITIC BLADE AND RECEPTACLE CONNECTOR

BOARD-TO-BOARD

The hermaphroditic blade and receptacle connector is a latest surface mount technology (SMT) connector and is intended for use with in-line board-to-board applications.

KEY FEATURES

- Available in 2, 4, and 6 positions
- Connector mates to itself
- Single part to be stocked and placed onto pcb per position
- Connector mates and unmates horizontally and vertically
- Connector can be articulated from 90° to 180°
- Tape and reel packed for high speed SMT processes
- Low profile flat surface is compatible with SMT and reflow processing
- Rounded corners to minimize shadowing
- Redundant SMT pads
- Optional 2, 4 and 6 position dust cover available
- RoHS compliant

APPLICATIONS

- LED Lighting Controls
- LED Lighting Strips
- Channel Lettering

ELECTRICAL

- Operating Current : 6 AMPS
- Operating Voltage : 125VAC/125VDC
- Dielectric Withstanding Voltage : 1500VAC

MECHANICAL

- Operating Temperature: -40°C to +105°C

MATERIALS

- Housings: UL 94V-0 high temperature resistant thermoplastic
- Contacts: Copper Alloy, tin over nickel plated
- Dust Cover : Polybutylene terephthalate (PBT)

STANDARDS & SPECIFICATIONS

- Board-to-Board Application Specification: [114-13225](#)
- Board-to-Board Product Specification: [108-2342](#)
- UL and cUL recognized : File No. E28476

PRODUCT OFFERING





Blade and Receptacle SMT Connectors

Part Number	Position	Color
2058703-1	2	White
2058703-2	4	White
2058703-3	6	White
1-2058703-1	2	Black
1-2058703-2	4	Black
1-2058703-3	6	Black

Dust Cover

Part Number	Position	Color
2058128-1	2	Natural
2058128-2	4	Natural
2058128-3	6	Natural
1-2058128-1	2	Black
1-2058128-2	4	Black
1-2058128-3	6	Black

Board-to-Board



2058703-3/
1-2058703-3

Technical drawing showing three types of identification plates (2058120-1, 2058120-2, 2058120-3) with dimensions and a detail view.

Detail View (Top):

- Text: TOP
- Width: 9.85 [0.390]
- Height: 5.95 [0.230]
- Radius: R0.95 [0.035]
- Feature: TYP

Plate 2058120-1:

- Width: 9.85 [0.386]
- Height: 5.90 [0.217]
- Feature: E

Plate 2058120-2:

- Width: 17.80 [0.701]
- Height: 5.90 [0.217]
- Feature: E

Plate 2058120-3:

- Width: 25.80 [1.016]
- Height: 5.90 [0.217]
- Feature: E

PRODUCT OFFERING AND DIMENSIONS


Wire-to-Board

Housings

Part Number	Position	Color
2058299-1	2	Natural
2058299-2	4	Natural
2058299-3	6	Natural
1-2058299-1	2	Black
1-2058299-2	4	Black
1-2058299-3	6	Black

Contacts

2058301-1	Blade Contact
2058301-2	Blade Contact - Loose Piece
2058302-1	Socket Contact
2058302-2	Socket Contact - Loose Piece



TE TECHNICAL SUPPORT CENTER

Internet:	te.com/help
USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com/hermaphroditic-connectors

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

©2025 TE Connectivity. All Rights Reserved.

06-25