

SPECIFICATIONS

MODEL	YELLOW LAMP LED
PART NO.	LY530

[Contents]

1.	Devices -----	2
2.	Outline Dimensions -----	2
3.	Absolute Maximum Ratings -----	3
4.	Electro-Optical Characteristics -----	4
5.	Reliability Tests -----	5
6.	Characteristic Diagrams -----	6
7.	Bin Code Description -----	8
8.	Packing -----	9
9.	Soldering Profile -----	12
10.	Reference -----	13
11.	Precaution For Use -----	14

<060814> Rev. 0.4

LY530



SEOUL SEMICONDUCTOR CO., LTD.


148-29, Kasan-Dong, Keumchun-Gu, Seoul, Korea

TEL : 82-2-3281-6269 FAX : 82-2-857-5430

1. DEVICES

Part Number	Lens		Source	
	Color	Diffusion	Dice Source	Color
LY530	Water Clear	Non-Diffused	AlInGaP/GaP	Yellow

2. OUTLINE DEMENSIONS



- Notes :
1. All dimensions are in millimeters.
 2. Protruded epoxy is 1.0mm maximum.

<060814> Rev. 0.4

LY530



SEOUL SEMICONDUCTOR CO., LTD.

148-29, Kasan-Dong, Keumchun-Gu, Seoul, Korea

TEL : 82-2-3281-6269 FAX : 82-2-857-5430

3. ABSOLUTE MAXIMUM RATINGS (at $T_a = 25^{\circ}\text{C}$)

Item	Symbol	Value	Unit
DC Forward Current	I_F	30	mA
Forward Peak Pulse Current	I_{FP}^1	100	mA
Reverse Voltage	V_R	5	V
Power Dissipation	P_D	100	mW
Operating Temperature	T_{opr}	-40 ~ 100	$^{\circ}\text{C}$
Storage Temperature	T_{stg}	-50 ~ 105	$^{\circ}\text{C}$
Solder Temperature	T_S	260 $^{\circ}\text{C}$ for 10 second ²	$^{\circ}\text{C}$

Notes : 1. $t \leq 0.1\text{ms}$, $D = 1/10$

2. 3mm below seating plane

4. ELECTRO-OPTICAL CHARACTERISTICS (at $I_F = 20\text{mA}$, $T_a = 25^\circ\text{C}$)

Item	Symbol	Value			Unit
		Min.	Typ.	Max.	
Luminous Intensity ¹	I_V	3000	4500	-	mcd
Dominant Wavelength	λ_d	584	590	596	nm
Forward Voltage	V_F	1.9	2.2	2.6	V
View Angle	$2\theta_{1/2}$	30			deg.
Reverse Current (at $V_R = 5\text{V}$)	I_R	-	-	5	μA

Note : 1. Luminous Intensity Tolerance $\pm 10\%$

5. RELIABILITY TESTS

Item	Condition	Note	Failures
Life Test	$T_a = \text{RT}, I_F = 30\text{mA}$	1000hrs	0/22
High Temperature Operating	$T_a = 100^\circ\text{C}, I_F = 10\text{mA}$	1000hrs	0/22
Low Temperature Operating	$T_a = -40^\circ\text{C}, I_F = 20\text{mA}$	1000hrs	0/22
Thermal Shock	$T_a = -50^\circ\text{C}$ (30min) $\sim$ 105° (30min) (Transfer time : 5sec, 1Cycle = 1hr)	100cycles	0/50
Resistance to soldering Heat	$T_s = 255 \pm 5^\circ\text{C}, t = 10\text{sec}$	1 time	0/22
ESD (Human Body Model)	1kV, 1.5k Ω ; 100pF	1 time	0/22
High Temperature Storage	$T_a = 105^\circ\text{C}$	1000hrs	0/22
Low Temperature Storage	$T_a = -50^\circ\text{C}$	1000hrs	0/22
Temperature Humidity Storage	$T_a = 85^\circ\text{C}, RH = 85\%$	1000hrs	0/22
Temperature Humidity Operating	$T_a = 85^\circ\text{C}, RH = 85\%$ $I_F = 15\text{mA}$	100hrs	0/22

< Judging Criteria For Reliability Tests >

V_F	USL ¹ $\times$ 1.2
I_R	USL $\times$ 2.0
I_V	LSL ² $\times$ 0.7

Notes : 1. USL : Upper Standard Level 2. LSL : Lower Standard Level.

<060814> Rev. 0.4

LY530




SEOUL SEMICONDUCTOR CO., LTD.


148-29, Kasan-Dong, Keumchun-Gu, Seoul, Korea

TEL : 82-2-3281-6269 FAX : 82-2-857-5430


6. CHARACTERISTIC DIAGRAMS




Off Axis Angle vs. Relative Intensity




Forward Voltage vs. Forward Current




Forward Current vs. Relative Intensity



Ambient Temperature vs. Forward Current




Wavelength vs. Relative Intensity



Ambient Temperature vs. Relative Intensity

7. BIN CODE DESCRIPTION

BIN CODE		
Forward Voltage	Color Ranks	Intensity
D	1	2



Forward Voltage (V) @ $I_F = 20\text{mA}$		
BIN CODE	Min.	Max.
A	1.9	2.0
B	2.0	2.1
C	2.1	2.2
D	2.2	2.3
E	2.3	2.4
F	2.4	2.5
G	2.5	2.6

Dominant Wavelength (nm) @ $I_F = 20\text{mA}$		
BIN CODE	Min.	Max.
1	584	590
2	590	596

Intensity (mcd) @ $I_F = 20\text{mA}$		
BIN CODE	Min.	Max.
1	3000	4000
2	4000	4500
3	4500	5000
4	5000	7000

8. PACKING


1) Bulk Packing

(1) Antistatic poly vinyl bag apply

Poly bag:

5 ϕ Lamp Series : 500pcs


3 ϕ Lamp Series : 500pcs



(2) Inner box structure


Box : 2 poly bags

		P/O No.	
Lot No			
SEOUL SEMICONDUCTOR CO.,LTD			
TEL : (02) 3281-6269			



(3) Outer box structure

Box : 27 boxes



<060814> Rev. 0.4

LY530




SEOUL SEMICONDUCTOR CO., LTD.

148-29, Kasan-Dong, Keumchun-Gu, Seoul, Korea


TEL : 82-2-3281-6269 FAX : 82-2-857-5430

2) Tapping Outline Dimensions



Package Dimensions (unit : mm)			
Ho*		P	12.7±0.5
W	18.0 ^{+1.0} _{-0.5}	Po	12.7±0.3
W0	13.0±0.3	F	2.54±0.5
W1	1.0±0.5	Do	φ4.0±0.5
W2	9.0±0.5		

* Remark : Ho - users define.




1 Box contain quantity.

* 3φ Lamp Series : 3000pcs


* 5φ Lamp Series : 2000pcs

3) Forming Outline Dimensions



Package Dimensions (unit : mm)			
H *		W2	9.0 ± 0.5
Ho *		P	12.7 ± 0.5
H1 *		Po	12.7 ± 0.3
W	$18.0^{+1.0}_{-0.5}$	F	5.0 ± 0.5
Wo	13.0 ± 0.3	Do	$\phi 4.0 \pm 0.5$
W1	1.0 ± 0.5		

* Remark : H / Ho / H1- users define.



1 Box contain quantity.


* 3 ϕ Lamp Series : 2000pcs

* 5 ϕ Lamp Series : 1500pcs

9. SOLDERING PROFILE

1) Wave Soldering Conditions / Profile

- Preliminary heating to be at 85°C(120 °C max) for 20 seconds(60 seconds max).
- Soldering heat to be at 235 °C (260°C max) for 5 seconds (10 seconds max.)
- Soak time above 200 °C is 5 seconds



2) Hand Soldering conditions

- Not more than 5 seconds at max. 300°C, under Soldering iron.

Note : In case the soldered products are reused in soldering process, we don't guarantee the products.

10. PART NUMBERING SYSTEM

1	2	3	4	5	6	7	8		A	B	C
L	*	*	*	*	*	*	*	-	*	*	*

1) Lamp LED initial

2) Color

U : Ultra Violet, B : Blue (460~490), C : Cyan (490~510),
T : True Green (510~540), G : Yellow-Green (540~580)
Y : Yellow (580~600) O : Orange (600~620) R : Red (620~700)
W : White M : Warm I : Infrared

3) If the products have 2 or 3chips

GR : Green + Red (according to wavelength), FL : Full color

4) Outline type

1 : 3x2(square), 2 : 5x2(square), 3 : Phi3, 5 : Phi 5 ,
6 : 3Phi Oval, 7 : 5Phi Oval

5) Half angle

1: ~14°, 2: 15~24° , 3: 25~34°, 4: 35~44°, 5 : 45~54°... 0 : more than 100°

6) 1st Development according to a chip

7) 2nd Development (other material)

D : diffused C : colored Z : zener chip attached

8) Stand off type

A, B, C : Bin cord description A: IV, B: WD C: VF

11. PRECAUTION FOR USE

- 1) In order to avoid the absorption of moisture, it is recommended to store in the dry box (or desiccators) with a desiccant .
- 2) In case of more than 1 week passed after opening or change color of indicator on desiccant components shall be dried 10-12Hr, at $60\pm5^{\circ}\text{C}$.
- 3) In case of supposed the components is humid, shall be dried dip-solder just before, 12Hr at $80\pm5^{\circ}\text{C}$ or 10Hr at $100\pm5^{\circ}\text{C}$.
- 4) Any mechanical force or any excess vibration shall not be accepted to apply during cooling process to normal temp. after soldering.
- 5) Quick cooling shall not be avoid.
- 6) Components shall not be mounted on warped direction of PCB.
- 7) Anti radioactive ray design is not considered for the products listed here in.
- 8) This device should not be used in any type of fluid such as water, oil, organic solvent and etc. When washing is required, IPA should be used.
- 9) When the LEDs are illuminating, operating current should be decided after considering the ambient maximum temperature.
- 10) LEDs must be stored to maintain a clean atmosphere. If the LEDs are stored for 3 months or more after being shipped from SSC, a sealed container with a nitrogen atmosphere should be used for storage.
- 11) The LEDs must be soldered within seven days after opening the moisture-proof packing.
- 12) Repack unused products with anti-moisture packing, fold to close any opening and then store in a dry place.
- 13) The appearance and specifications of the product may be modified for improvement without notice.