





REV.	DATE	ECR NO.	DESCRIPTION
A	04/28/97	—	CHANGE GOLD PLATING SPEC.
B	09/30/08	—	UPDATE DRAWING FORMAT.



RECOMMENDED
CABLE STRIPPING DIM'S



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. NICKEL PL. 100 MIN. OVER COPPER PL. 50 MIN.
2. GOLD PL. 15 MIN. OVER NICKEL PL. 50 MIN. OVER COPPER PL. 50 MIN.
3. TEFLON MIL-P-19468.

						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex							
8						UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm		DRAWN		GRS							09/30/08		
7								CHECKED											
6								ISSUED											
5								SHEET		1 OF 1				PART DESCRIPTION BNC CRIMP PLUG (RG–6 PLENUM/ BELDEN 1695A – 75 ohms)					
4	FERRULE	BRASS	NICKEL	1		UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"													
3	CONTACT PIN	BRASS	GOLD	1										PART NO. 112958					
2	INSULATOR	PTFE	NATURAL	1															
1	BODY	BRASS	NICKEL	1										DWG. NO. 112958.DWG					
	DESCRIPTION	MATERIAL	FINISH	QTY		DO NOT SCALE DRAWING		CAD FILE		C:/112/112958.DWG									REV. B