


POWER OVER ETHERNET (PoE) MAGNETICS

10/100BASE-TX VoIP Magnetics Modules



- IEEE 802.3af/ANSI X3.263 compliant performance
- Suitable for End-span and Mid-span PoE applications
- 350 mA current capability
- Designed for IP phone or switch applications
- Compact footprint
- Some models offer AutoMDIX capability


Electrical Specifications @ 25°C — Operating Temperature 0°C to 70°C

Part Number	Ports	Insertion Loss (dB MAX)	Return Loss (dB MIN @ 100 Ω)					Differential to Common Mode Rejection (dB MIN)			Crosstalk (dB MIN)			Hipot (Vrms MIN)	DC Resistance Balance ≤ (%)
			1-100 MHz	1-30 MHz	40 MHz	50 MHz	60-80 MHz	30 MHz	60 MHz	100 MHz	30 MHz	60 MHz	100 MHz		
H1180 ^{1,3}	1	-1.2	-16	-14	-13	-12	-12	-43	-37	-33	-45	-40	-35	1500	—
H1187 ^{1,3}	1	-1.2	-16	-14	-13	-12	-12	-43	-37	-33	-45	-40	-35	1500	—
H1197 ^{1,3}	1	-1.2	-16	-14	-13	-12	-12	-43	-37	-33	-45	-40	-35	1500	—
H2019 ¹	1	-1.2	-16	-14	-13	-12	-12	-43	-37	-33	-45	-40	-35	1500	3.5
H2005A	2	-1.2	-16	-14	-13	-12	-12	-50	-43	-35	-43	-37	-33	1500	3.5
H2006A ¹	2	-1.2	-16	-14	-13	-12	-12	-43	-37	-33	-43	-37	-31	1500	3.5
H2008	2	-1.2	-16	-14	-13	-12	-12	-40	-35	-30	-43	-37	-33	1500	3.5
H2009 ¹	2	-1.1	-16	-14	-13	-12	-12	-43	-37	-33	-43	-37	-33	1500	3.5
H2014	4	-1.2	-16	-14	-13	-12	-12	-43	-37	-33	-45	-40	-35	1500	3.5
HX2019 ^{1,2}	1	-1.4	-18	-14	-13	-13	-12	—	—	—	-45	-40	-35	1500	3.5

1. Suitable for Auto MDIX applications
2. Extended temperature (-40°C to +85°C)
3. Recommended parts for mid-span PoE applications

Mechanicals


H1180



Weight 0.6 grams
Tape & Reel 500/reel
Tube65/tube

Dimensions: $\frac{\text{Inches}}{\text{mm}}$ Unless otherwise specified, all tolerances are $\pm \frac{.010}{.025}$

H1187



Weight 0.6 grams
Tape & Reel 500/reel
Tube 70/tube

POWER OVER ETHERNET (PoE) MAGNETICS


10/100BASE-TX VoIP Magnetics Modules



Pulse
A TECHNITROL COMPANY

Mechanicals


H1197



Dimensions: $\frac{\text{Inches}}{\text{mm}}$ Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

Weight 2.8 grams
Tape & Reel 600/reel
Tube 45/tube


H2019, HX2019



Weight 1.0 grams
Tape & Reel 600/reel
Tube 45/tube

Dimensions: $\frac{\text{Inches}}{\text{mm}}$ Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

H2005A



Weight 2.7 grams
Tape & Reel 300/reel
Tube 25/tube


POWER OVER ETHERNET (PoE) MAGNETICS

10/100BASE-TX VoIP Magnetics Modules




Mechanicals (continued)

H2006A, H2008



H2009




Weight 2.4 grams
 Tape & Reel 350/reel
 Tube 35/tube

Dimensions: $\frac{\text{Inches}}{\text{mm}}$ Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

Weight 1.6 grams
 Tape & Reel 300/reel
 Tube 35/tube

H2014



Dimensions: $\frac{\text{Inches}}{\text{mm}}$ Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

Weight 5.0 grams
 Tape & Reel 250 /reel
 Tube 15/tube


POWER OVER ETHERNET (PoE) MAGNETICS

10/100BASE-TX VoIP Magnetics Modules




Schematics


H1180, H1187




H1197




H2019, HX2019



H2005A



H2006A




NOTE: The H2006A is suitable for AutoMDIX applications.

POWER OVER ETHERNET (PoE) MAGNETICS


10/100BASE-TX VoIP Magnetics Modules



Schematics (continued)



NOTE: The H2009 is suitable for AutoMDIX applications.



For More Information:

UNITED STATES (Worldwide)	UNITED KINGDOM (Northern Europe)	FRANCE (Southern Europe)	SINGAPORE (Southern Asia)	TAIWAN, R.O.C. (Northern Asia)	HONG KONG (Great China)	DISTRIBUTOR
12220 World Trade Drive San Diego, CA 92128 U.S.A. http://www.pulseeng.com TEL: 858 674 8100 FAX: 858 674 8262	1 & 2 Huxley Road The Surrey Research Park Guildford, Surrey GU2 5RE United Kingdom TEL: 44 1483 401700 FAX: 44 1483 401701	Zone Industrielle F-39270 Orgelet France TEL: 33 3 84 35 04 04 FAX: 33 3 84 25 46 41	150 Kampong Ampat #07-01/02 KA Centre Singapore 368324 TEL: 65 6287 8998 FAX: 65 6280 0080	3F-4, No. 81, Sec. 1 HsinTai Wu Road Hsi-Chih, Taipei Hsien Taiwan, R.O.C. Tel: 886 2 2698 0228 FAX: 886 2 2698 0948	19/F, China United Plaza 1008 Tai Nan West Street Cheung Sha Wan, Kowloon Hong Kong, China TEL: 852 2788 6588 FAX: 852 2776 1055	

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.

♻️ Printed on recycled paper. © Copyright, 2003, Pulse Engineering, Inc. All rights reserved.