


Product: [7956S](#) 

Composite Data, Audio, Video, Security and Control Cable



Product Description

Banana Peel® Composite - (1) Cat 5e 4-pair 24 AWG unshielded plus (2) Series 6 Coax with Duobond® IV Quad shield, polyolefin insulation on the pairs; Gas-injected FPE insulation on the coax, PVC jackets, CMR rated. No overall jacket.

Technical Specifications

Product Overview

Suitable Applications:	CATV, Data
------------------------	------------

Physical Characteristics (Overall)

Conductor Count:	10
Total Number of Pairs:	4
Overall Nominal Diameter:	0.596 in

Temperature Range

Installation Temp Range:	°C to +75°C
Operating Temp Range:	-5°C to +75°C

Mechanical Characteristics

Bulk Cable Weight:	90 lbs
Max. Pull Tension:	118 lbs

Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No

Suitability - Sunlight Resistance:	No
------------------------------------	----

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL 1666 Vertical Shaft
CSA Flammability:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
7956S 000500	None	Reel	500 ft	612825192268
7956S 0001000	None	Reel	1,000 ft	612825001690

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.62 Revision Date: 06-24-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.