ELFT SERIES PART NUMBERING SCHEME

REV	ECN	APPD
–	3600	JEC 12/11/98
A	4686	RN 12/28/05

ELF T _ _ _ _ _ _

TYPE (STRAIGHT PLUG)

NUMBER OF POSITIONS
WITHOUT MOUNTING EARS: 02–24
WITH MOUNTING EARS: 02–22

CENTERLINE SPACING
1=.197" (5MM)
2=.200"

STYLE
5=TOP ACCESS
6=BOTTOM ACCESS

OPTIONS

COLOR/PLATING
0=BLACK, TIN (STANDARD)
1=BLACK, SELECTIVE GOLD
G=GREEN, TIN
1G=GREEN, SEL. GOLD

MOUNTING EARS
0E=BLACK, TIN
1E=BLACK, SEL. GOLD
GE=GREEN, TIN
EG=GREEN, SEL. GOLD

CONSULT PCD FOR PART NO. AND AVAILABILITY OF FOLLOWING OPTIONS:
* CUSTOM COLORS
* CUSTOM MARKING
* CUSTOM KEYING
* SELECTIVE CONTACT LOADING

RATINGS
CURRENT – 15A
VOLTAGE – 300V
U.L. FILE NO. E83421

RATINGS
CURRENT – 15A
VOLTAGE – 300V
CSA FILE NO. LR69703

DIN VDE 0627:1986
DIN VDE 0110–1:1989
EN 60947–1:1991
EN 60947–7–1:1992

CURRENT – 15A
VOLTAGE – 300 V
TUV FILE NO. 20396

INSTALLATION RECOMMENDATIONS:
WIRE RANGE: AWG #14–26, STRANDED OR SOLID; AWG #12 STRANDED
WIRE STRIP LENGTH: .310"
TIGHTENING TORQUE: 7 LB–IN.

MATERIALS:
HOUSING: PPO, UL 94 V–0
CONTACT: COPPER ALLOY, OPTIONAL FINISH
SCREW: STEEL, NICKEL FINISH
WIRE CLAMP: COPPER ALLOY, NICKEL FINISH

MAX OPERATING TEMPERATURE:
105°C

DIMENSIONS	TOLERANCES	PROJECTION
ANSI Y14.5M	.XX ±.01	
UNITS: INCHES	.XXX ±.005	
ACAD FILE	ANGLES ±2°	

Amphenol Pcd
SPECIFICATION DRAWING

ENGR
J. WILKINSON 11/8/98

CHKD
A. PATRIE 12/4/98

APPD
J. CAHALY 12/11/98

TITLE
ELFT SERIES
PLUGGABLE TERMINAL
BLOCK, STRAIGHT

ORIGINAL STAMPED IN RED

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC. PEABODY, MA

SIZE	DWG NO.	REV
A	ELFT02150	B

CODE: 58982	SCALE: NONE	SHEET 1 OF 2



WITHOUT MOUNTING EARS

L=NUM OF POS X CL SPACING





WITH MOUNTING EARS

L=NUM OF POS X CL SPACING



SIZE	DWG NO.	REV
A	ELFT02150	B
CODE: 58982	SCALE: NONE	SHEET 2 OF 2