

# MCC

Micro Commercial Components



Micro Commercial Components  
20736 Marilla Street Chatsworth  
CA 91311  
Phone: (818) 701-4933  
Fax: (818) 701-4939

## Features

- Lead Free Finish/RoHS Compliant (Note 1) ("P" Suffix designates RoHS Compliant. See ordering information)
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Rating to 1000V PRV
- Ideal for printed circuit board
- Low forward voltage drop, high current capability.
- UL Recognized File # E165989
- Halogen free available upon request by adding suffix "-HF"

## Maximum Ratings

- Operating Temperature: -55°C to +150°C
- Storage Temperature: -55°C to +150°C
- Mounting torque: 5in-lbs.

MCC Catalog Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
GBJ20005	GBJ20005	50V	35V	50V
GBJ2001	GBJ2001	100V	70V	100V
GBJ2002	GBJ2002	200V	140V	200V
GBJ2004	GBJ2004	400V	280V	400V
GBJ2006	GBJ2006	600V	420V	600V
GBJ2008	GBJ2008	800V	560V	800V
GBJ2010	GBJ2010	1000V	700V	1000V

## Electrical Characteristics @ 25°C Unless Otherwise Specified


Average Forward Current	$I_{F(AV)}$	20 A	$T_c = 100^\circ C$
Peak Forward Surge Current	$I_{FSM}$	240A	8.3ms, half sine
Maximum Instantaneous Forward Voltage	$V_F$	1.05V	$I_{FM} = 10.0 A$ $T_J = 25^\circ C$
Maximum DC Reverse Current At Rated DC Blocking Voltage	$I_R$	$10 \mu A$ $500 \mu A$	$T_J = 25^\circ C$ $T_J = 125^\circ C$
Typical thermal resistance	$R_{GJC}$	0.8°C/W	
Typical Junction Capacitance	$C_J$	60 pF	Measured at 1.0MHz, $V_R=4.0V$

\*Pulse Test: Pulse Width 300μsec, Duty Cycle 1%

Notes: 1. High Temperature Solder Exemption Applied, see EU Directive Annex Notes 7.

GBJ20005  
THRU  
GBJ2010

20 Amp  
Glass Passivated  
Bridge Rectifier  
50 to 1000 Volts



DIMENSIONS					NOTE	
DIM.	INCHES		MM			
	MIN	MAX	MIN	MAX		
A	1.170	1.190	29.70	30.30		
B	.780	.800	19.70	20.30		
C	.670	.710	17.00	18.00		
D	.019	.019	4.70	4.90		
E	.430	.440	10.80	11.20		
F	.090	.110	2.30	2.70		
G	.120	.130	3.10	3.40		
H	.130	.150	3.40	3.80		
I	.170	.190	4.40	4.80		
J	.100	.110	2.50	2.90		
K	.020	.030	0.60	0.80		
L	.080	.090	2.00	2.40		
M	.040	.040	0.90	1.10		
N	.390	.400	9.80	10.20		
O	.290	.300	7.30	7.70		
P	.150	.170	3.80	4.20		

[www.mccsemi.com](http://www.mccsemi.com)

**RATING AND CHARACTERISTIC CURVES**  
**GBJ20005 thru GBJ2010**

FIG.1 - FORWARD CURRENT DERATING CURVE




FIG.2 - MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3 - TYPICAL JUNCTION CAPACITANCE




FIG.4 - TYPICAL FORWARD CHARACTERISTICS





FIG.5 - TYPICAL REVERSE CHARACTERISTICS



## Ordering Information :

Device	Packing
Part Number-BP	Bulk: 750pcs/Box

Note : Adding "-HF" suffix for halogen free, eg. Part Number-BP-HF

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.