









- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X±0.4
X.XX±0.25
 3. TERM. NOS. FOR REFERENCE ONLY.
 4. RATING 0.1A @30V DC
 - ▲ 5. MATERIALS:
CONTACT/TERMINALS: SILVER PLATE
HOUSING: PBT UL94VO
BASE: PA66 UL94VO
ACTUATOR: PA66 UL94VO
CONTACT RESISTANCE: 100 MILLI-OHM (INITIAL)
 - ▲ 6. TIMING: NON-SHORTING
 8. OPERATING FORCE: 230± 50GF
 9. TRAVEL: MOMENTARY
2MM TO MAKE
3MM OVERALL
 10. ELECTRICAL LIFE: 10000 CYCLES
 11. OPERATING TEMP: -20°C TO +70°C
 12. ▲ DENOTES CRITICAL PARAMETER.
 13. 2002/95/EC (ROHS) COMPLIANT

E-SWITCH®

TITLE PBH2UOANAGV

B	19670	UPDATE CIRCUIT DIAGRAM	2/10/11	BGL
A	16400	RELEASED FOR PRODUCTION	8/31/06	BO
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	2.5:1	DATE	8/31/2006	DR	BO	DWG	Q960019	REV	B
-------	-------	------	-----------	----	----	-----	---------	-----	---