

4.8mm Semi-Lens Silicon PIN Photodiode EAPDLP04SCAA4



Features

- Fast response times
- High photo sensitivity
- Small junction capacitance
- Pb free
- The product itself will remain within RoHS compliant version.

Description

- EAPDLP04SCAA4 is a high speed and sensitive PIN photodiode in a flat side view plastic package. Due to its water clear epoxy the device is sensitive to visible and infrared radiation.

Applications

- High speed photo detector
- Camera
- Optoelectronic switch
- VCRs , Video camera

Device Selection Guide

Chip Materials	Lens Color
GaAlAs	Water clear

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit
Reverse Voltage	V _R	32	mA
Power Dissipation	P _d	150	mW
Operating Temperature	T _{opr}	-25 ~ +85	°C
Storage Temperature	T _{stg}	-40 ~ +85	°C
Soldering Temperature(*1)	T _{sol}	260	°C

Notes: *1: Soldering time ≤ 5 seconds.


:

Electro-Optical Characteristics (Ta=25°C)


Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Rang of Spectral Bandwidth	$\lambda_{0.5}$	400	-----	1100	nm	-----
Wavelength of Peak Sensitivity	λ_p	-----	940	-----	nm	-----
Open-Circuit Voltage	V_{OC}	-----	0.41	-----	V	Ee=5m W/cm ² λ_p =940nm
Short- Circuit Current	I_{SC}	---	18	-----	uA	Ee=1m W/cm ² λ_p =940nm
Reverse Light Current	I_L	10.2	18	-----	uA	Ee=1m W/cm ² λ_p =940nm V_R =5V
Dark Current	I_d	----	5	30	nA	Ee=0m W/cm ² V_R =10V
Reverse Breakdown	B_{VR}	32	170	-----	V	Ee=0m W/cm ² I_R =100μA
Total Capacitance	C_t	----	25	----	pF	Ee=0m W/cm ² V_R =3V f=1MHZ
Rise/Fall Time	tr/tf	----	50/50	----	ns	V_R =10V R_L =1KΩ

Typical Electro-Optical Characteristics Curves


Power Dissipation vs. Ambient Temperature




Spectral Sensitivity




Dark Current vs. Ambient Temperature




Reverse Light Current vs. E_e






Package Dimension



Note: Tolerances unless dimensions ± 0.25 mm


Label Explanation




- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Dom. Wavelength Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number
- Reference: Identify Label Number

Packing Specification


■ Anti-electrostatic bag



■ Inner Carton



■ Outside Carton



■ Packing Quantity

1. 500 PCS/1 Bag, 5 Bags/1 Inner Carton
2. 10 Inner Cartons/1 Outside Carton

Notes

1. Above specification may be changed without notice. Everlight Americas will reserve authority on material change for above specification.
2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. Everlight Americas assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
3. These specification sheets include materials protected under copyright of Everlight Americas corporation. Please don't reproduce or cause anyone to reproduce them without Everlight Americas's consent.