





No mounting hardware selected
with 3,05 (.120) mounting hole



A ± 0,38 (.015)	B ± 0,13 (.005)	C ± 0,13 (.005)	D ± 0,13 (.005)	E ± 0,38 (.015)	L ± 0,25 (.010)	W ± 0,41 (.016)	K ± 0,32 (.013)
53,04 (2.088)	38,38 (1.511)	47,04 (1.852)	7,90 (.311)	12,55 (.494)	0,76 (.030)	6,94 (.273)	1,21 (.048)

25 crimp signal contacts, part number 031-1007-078 kitted with each connector

DESCRIPTION	MATERIAL	FINISH
Insulator	DAP 2 Piece	None, (Color White), Copper alloy retention clips
Shells	Steel	Yellow Chromate over Zinc
Signal Contacts	Copper alloy	50 u inch Gold over Ni with Stainless Steel Sleeve
Unless otherwise specified, dimensions are in mm & (in.) Tolerances are (.XXX = mm) Decimals Angles .X ± 0,20 (.008) X° ± 1.0° .XX ± 0,10 (.004) .XXX ± 0,05 (.002)		Issue Date: 21-Aug-99
		Cannon ITT Industries
		CONNECTOR, RECEPTACLE, ELECTRICAL D-SUBMINIATURE 25 POSITION CRIMP
		PART NO. DBMAM25S