




LOC	DIST	REVISIONS					
AJ	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H2	REVISED PER ECO 06-029805	2/5/2007	DW	JL



- 1 ZINC PER QQ-Z-363.
- 2 PHOSPHOR BRONZE PER ASTM-B-139.
- 3 POLYESTER PER ASTM-D-3220.
- 4 TIN PLATE PER ASTM-B-545, 2.54 μ m [.000100] MIN THICK.
- 5 GOLD PLATE PER MIL-G-45204 0.76 μ m [.000030] MINIMUM THICK.
- 6 SILVER PLATE PER QQ-S-365 2.54 μ m [.000100] MINIMUM THICK.
- 7. FOR USE WITH .095 MAX THK PC BOARD.
- 8. SEE INSTRUCTION SHEET 408-9889.
- 9 TIN-LEAD PLATE PER ASTM-B-545, 2.54 μ m[.000100] MIN THICK.

OBSOLETE	4	5	9-221123-0
OBSOLETE	9	4	221123-3
	9	5	221123-2
OBSOLETE	9	6	221123-1
SHELL PLATING		CONTACT PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LIPPERT 1-18-93		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK A. GABANY 1-19-93			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. GABANY 1-19-93		NAME JACK, VERTICAL, PCB, 50 Ohm, COMMERCIAL BNC
	0 PLC ± -		PRODUCT SPEC		
	1 PLC ± -		108-12078		
	2 PLC ± 0.08 [.003]		APPLICATION SPEC		
3 PLC ± -		—		SIZE	
4 PLC ± -		—		CAGE CODE	
ANGLES ± -		WEIGHT —		DRAWING NO	
MATERIAL		FINISH		RESTRICTED TO	
SEE NOTES 1 - 3		SEE NOTES 4 - 6		A2 00779 C=221123 —	
CUSTOMER DRAWING				SCALE 5:1	
				SHEET 1 of 1	
				REV H2	