

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

91716-2013

Status:


Active

Overview:

RAST 2.5 Connector System

Description:

2.50mm Pitch Appli-Mate® RAST 2.5 IDT Housing, Direct/Indirect, Female, 7 Circuits, Removed Position Keys B, D, E, F & H



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-99020-0040 \(PDF\)](#)
- [Application Specification AS-99033-0008 \(PDF\)](#)
- [Packaging Specification PK-90871-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Comments

IDT and Solder Connectors

91716

"This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options."

Yes

[RAST 2.5 Connector System](#)

RAST 2.5

822350166447

RAST standard interface

Crimp Quality Equipment

Overview

Product Name

UPC

Use With

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Gender

Glow-Wire Compliant

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

6

6

Natural (White)

10

94V-0

Female

No

None

Phosphor Bronze

Tin

Tin

Nylon

1.704/g

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

91716Series

Mates With

Appli-Mate RAST 2.5 Header [90861](#) , [90860](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Tool for Appli-Mate RAST2.5, RAST Signal, and R-Power Connectors	0638272900
RAST 2.5 Semi-Automatic Terminator Machine	0623006200

Number of Rows	1
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-20C to +120C
Termination Interface: Style	IDT or Pierce
Wire Size AWG	22, 24

Electrical

Current - Maximum per Contact	2A, 4A
Voltage - Maximum	32V AC

Material Info

Reference - Drawing Numbers

Application Specification	AS-99033-0008
Packaging Specification	PK-90871-001
Product Specification	PS-99020-0040
Sales Drawing	SD-91716-001

This document was generated on 06/30/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[91716-2013](#)