


| ITEM | Q'TY | PART NUMBER | PART DESCRIPTION                |
|------|------|-------------|---------------------------------|
| 1    | 1    | SLM-XXX     | Molded Self-Retaining LED Mount |
| 2    | 1    | 5XX-F       | T1 ¾ (5mm) Flanged LED          |

| REV. | DESCRIPTION              | DATE     | APPROVED |
|------|--------------------------|----------|----------|
| A    | Engineering Release.     | 06/14/07 | M. C.    |
| B    | Updated Uncut Leads      | 06/06/08 | M. C.    |
| C    | Updated Uncut Leads Note | 12/24/08 | T. Y.    |
| D    | Updated P/N's on Page 2  | 09/16/09 | T. Y.    |
| E    | Updated LED Protrusion   | 10/19/09 | T. Y.    |



| PART NO. | SH ( Ref.)   | H             |
|----------|--------------|---------------|
| SLM-140  | .140 (3.6mm) | .285 (7.1mm)  |
| SLM-150  | .150 (3.8mm) | .295 (7.2mm)  |
| SLM-160  | .160 (4.1mm) | .305 (7.7mm)  |
| SLM-170  | .170 (4.3mm) | .315 (8.0mm)  |
| SLM-180  | .180 (4.6mm) | .325 (8.3mm)  |
| SLM-190  | .190 (4.8mm) | .335 (8.5mm)  |
| SLM-200  | .200 (5.1mm) | .345 (8.8mm)  |
| SLM-210  | .210 (5.3mm) | .355 (9.0mm)  |
| SLM-220  | .220 (5.6mm) | .365 (9.3mm)  |
| SLM-230  | .230 (5.8mm) | .375 (9.5mm)  |
| SLM-240  | .240 (6.1mm) | .385 (9.8mm)  |
| SLM-250  | .250 (6.4mm) | .395 (10.0mm) |
| SLM-260  | .260 (6.6mm) | .405 (10.3mm) |
| SLM-270  | .270 (6.9mm) | .415 (10.5mm) |

| PART NO. | SH ( Ref.)    | H             |
|----------|---------------|---------------|
| SLM-280  | .280 (7.1mm)  | .425 (10.8mm) |
| SLM-290  | .290 (7.4mm)  | .435 (11.0mm) |
| SLM-300  | .300 (7.6mm)  | .445 (11.3mm) |
| SLM-310  | .310 (7.9mm)  | .455 (11.6mm) |
| SLM-320  | .320 (8.1mm)  | .465 (11.8mm) |
| SLM-330  | .330 (8.4mm)  | .475 (12.1mm) |
| SLM-340  | .340 (8.6mm)  | .485 (12.3mm) |
| SLM-350  | .350 (8.9mm)  | .495 (12.6mm) |
| SLM-360  | .360 (9.1mm)  | .505 (12.8mm) |
| SLM-370  | .370 (9.4mm)  | .515 (13.1mm) |
| SLM-380  | .380 (9.7mm)  | .525 (13.3mm) |
| SLM-390  | .390 (9.9mm)  | .535 (13.6mm) |
| SLM-400  | .400 (10.2mm) | .545 (13.8mm) |
| SLM-410  | .410 (10.4mm) | .555 (14.1mm) |

| PART NO. | SH ( Ref.)    | H             |
|----------|---------------|---------------|
| SLM-420  | .420 (10.7mm) | .565 (14.3mm) |
| SLM-430  | .430 (10.9mm) | .575 (14.6mm) |
| SLM-440  | .440 (11.2mm) | .585 (14.9mm) |
| SLM-450  | .450 (11.4mm) | .595 (15.1mm) |
| SLM-470  | .470 (11.9mm) | .615 (15.6mm) |
| SLM-490  | .490 (12.4mm) | .635 (16.1mm) |
| SLM-510  | .510 (13.0mm) | .655 (16.6mm) |
| SLM-530  | .530 (13.5mm) | .675 (17.1mm) |
| SLM-550  | .550 (13.8mm) | .695 (17.5mm) |
| SLM-570  | .570 (14.5mm) | .715 (18.2mm) |
| SLM-590  | .590 (15.0mm) | .735 (18.6mm) |
| SLM-610  | .610 (15.5mm) | .755 (19.2mm) |
| SLM-630  | .630 (16.0mm) | .775 (19.7mm) |
| SLM-650  | .650 (16.5mm) | .795 (20.2mm) |

| PART NO. | SH ( Ref.)    | H              |
|----------|---------------|----------------|
| SLM-670  | .670 (17.0mm) | .815 (20.7mm)  |
| SLM-690  | .690 (17.5mm) | .835 (21.2mm)  |
| SLM-710  | .710 (18.0mm) | .855 (21.7mm)  |
| SLM-730  | .730 (18.5mm) | .875 (22.2mm)  |
| SLM-750  | .750 (19.1mm) | .895 (22.7mm)  |
| SLM-770  | .770 (19.6mm) | .915 (23.2mm)  |
| SLM-790  | .790 (20.1mm) | .935 (23.7mm)  |
| SLM-810  | .810 (20.6mm) | .955 (24.3mm)  |
| SLM-830  | .830 (21.1mm) | .975 (24.8mm)  |
| SLM-850  | .850 (21.6mm) | .995 (25.3mm)  |
| SLM-870  | .870 (22.1mm) | 1.015 (25.8mm) |
| SLM-890  | .890 (22.6mm) | 1.035 (26.3mm) |

## ABSOLUTE MAXIMUM RATINGS ( $T_a = 25^\circ\text{C}$ )

|                                              |                                             |
|----------------------------------------------|---------------------------------------------|
| REVERSE VOLTAGE                              | 5V                                          |
| REVERSE CURRENT ( $V_R=5V$ )                 | 100 $\mu\text{A}$                           |
| OPERATING TEMPERATURE RANGE                  | -25 $^\circ\text{C}$ ~ 85 $^\circ\text{C}$  |
| STORAGE TEMPERATURE                          | -30 $^\circ\text{C}$ ~ 100 $^\circ\text{C}$ |
| LEAD SOLDERING TEMPERATURE (1/16" FROM BODY) | 260 $^\circ\text{C}$ for 5 Seconds          |

|                                                      |                          |                                                                                                                                                                 |                       |
|------------------------------------------------------|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|
| STANDARD TOLERANCE<br>( UNLESS OTHERWISE SPECIFIED ) |                          | <br>4 THOMAS, IRVINE, CA. 92618<br>TEL: (949) 951-8808 FAX: (949) 951-3974 |                       |
| <u>DECIMALS</u>                                      | <u>ANGULAR</u>           |                                                                                                                                                                 |                       |
| .X ± .1                                              | X° ± 1°                  |  <b>TITLE:</b> MOLDED, SELF-RETAINING LED ASSEMBLY                         |                       |
| .XX ± .01                                            |                          |                                                                                                                                                                 |                       |
| .XXX ± .005                                          |                          | <b>PART NO:</b> SLMXXX5XXX                                                                                                                                      |                       |
| DESIGNED:<br><b>Dan Beckman</b>                      | DATE:<br><b>06/14/07</b> | REVISION:<br><b>E</b>                                                                                                                                           |                       |
| CHECKED:<br><b>T. Yin</b>                            | DATE:<br><b>06/14/07</b> | <b>CAGE CODE :</b> 32559                                                                                                                                        | <b>SHEET # 1 OF 2</b> |
| CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.      |                          |                                                                                                                                                                 |                       |

| REV. | DESCRIPTION  | DATE | APPROVED |
|------|--------------|------|----------|
|      | SEE SHEET#1. |      |          |
|      |              |      |          |

| Assy Part No. | Chip      |                            |               | Lens Appearance | Absolute Max. Ratings |            |            |             | Electro-Optical Data @ 20mA |     |             | Viewing Angle<br>2 Θ ½<br>(Deg) | LED Part No. |
|---------------|-----------|----------------------------|---------------|-----------------|-----------------------|------------|------------|-------------|-----------------------------|-----|-------------|---------------------------------|--------------|
|               | Material  | Peak Wave Length<br>λp(nm) | Emitted Color |                 | Δλ<br>(nm)            | Pd<br>(mW) | If<br>(mA) | Peak If(mA) | Vf<br>(V)                   |     | Iv<br>(mcd) |                                 |              |
|               |           |                            |               |                 |                       |            |            |             | TYP                         | MAX | TYP         |                                 |              |
| SLMXXX5BWC    | GaN/SiC   | 430                        | BLUE          | WATER CLEAR     | -                     | 150        | 25         | 70          | 4.0                         | 4.5 | 30          | 25                              | 5BWC-F       |
| SLMXXX5BWD    | GaN/SiC   | 430                        | BLUE          | DIFFUSED        | -                     | 150        | 25         | 70          | 4.0                         | 4.5 | 15          | 40                              | 5BWD-F       |
| SLMXXX5BWT    | GaN/SiC   | 430                        | BLUE          | TINTED          | -                     | 150        | 25         | 70          | 4.0                         | 4.5 | 30          | 25                              | 5BWT-F       |
| SLMXXX5PGC    | GaP/GaP   | 555                        | PURE GREEN    | WATER CLEAR     | -                     | 80         | 30         | 150         | 2.2                         | 2.8 | 10          | 35                              | 5PGC-F       |
| SLMXXX5PGD    | GaP/GaP   | 555                        | PURE GREEN    | DIFFUSED        | -                     | 80         | 30         | 150         | 2.2                         | 2.8 | 10          | 40                              | 5PGD-F       |
| SLMXXX5PGT    | GaP/GaP   | 555                        | PURE GREEN    | TINTED          | -                     | 80         | 30         | 150         | 2.2                         | 2.8 | 10          | 35                              | 5PGT-F       |
| SLMXXX5GC     | GaP/GaP   | 568                        | GREEN         | WATER CLEAR     | -                     | 80         | 30         | 150         | 2.1                         | 2.8 | 40          | 35                              | 5GC-F        |
| SLMXXX5GD     | GaP/GaP   | 568                        | GREEN         | DIFFUSED        | -                     | 80         | 30         | 150         | 2.1                         | 2.8 | 25          | 40                              | 5GD-F        |
| SLMXXX5GT     | GaP/GaP   | 568                        | GREEN         | TINTED          | -                     | 80         | 30         | 150         | 2.1                         | 2.8 | 40          | 35                              | 5GT-F        |
| SLMXXX5YC     | GaAsP/GaP | 590                        | YELLOW        | WATER CLEAR     | -                     | 85         | 30         | 150         | 2.0                         | 2.8 | 40          | 35                              | 5YC-F        |
| SLMXXX5YD     | GaAsP/GaP | 590                        | YELLOW        | DIFFUSED        | -                     | 85         | 30         | 150         | 2.0                         | 2.8 | 25          | 40                              | 5YD-F        |
| SLMXXX5YT     | GaAsP/GaP | 590                        | YELLOW        | TINTED          | -                     | 85         | 30         | 150         | 2.0                         | 2.8 | 40          | 35                              | 5YT-F        |
| SLMXXX5HC     | GaAsP/GaP | 625                        | HE RED        | WATER CLEAR     | -                     | 80         | 30         | 150         | 2.0                         | 2.8 | 50          | 35                              | 5HC-F        |
| SLMXXX5HD     | GaAsP/GaP | 625                        | HE RED        | DIFFUSED        | -                     | 80         | 30         | 150         | 2.0                         | 2.8 | 40          | 40                              | 5HD-F        |
| SLMXXX5HT     | GaAsP/GaP | 625                        | HE RED        | TINTED          | -                     | 80         | 30         | 150         | 2.0                         | 2.8 | 50          | 35                              | 5HT-F        |
| SLMXXX5RC     | GaP/GaP   | 700                        | RED           | WATER CLEAR     | -                     | 45         | 20         | 80          | 2.1                         | 2.8 | 2           | 35                              | 5RC-F        |
| SLMXXX5RD     | GaP/GaP   | 700                        | RED           | DIFFUSED        | -                     | 45         | 20         | 80          | 2.1                         | 2.8 | 1.5         | 40                              | 5RD-F        |
| SLMXXX5RT     | GaP/GaP   | 700                        | RED           | TINTED          | -                     | 45         | 20         | 80          | 2.1                         | 2.8 | 2           | 35                              | 5RT-F        |

|                                                                                            |                          |                                                                                                                                                                    |             |
|--------------------------------------------------------------------------------------------|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| STANDARD TOLERANCE<br>( UNLESS OTHERWISE SPECIFIED )<br>$\pm 10\%$ ALL VALUES      ANGULAR |                          | <br>4 THOMAS, IRVINE, CA. 92618<br>TEL: (949) 951-8808    FAX: (949) 951-3974 |             |
|       |                          | TITLE: MOLDED, SELF-RETAINING LED ASSEMBLY                                                                                                                         |             |
|                                                                                            |                          | PART NO: SLMXXX5XXX                                                                                                                                                | REVISION: E |
| DESIGNED:<br><b>Dan Beckman</b>                                                            | DATE:<br><b>06/14/07</b> | CAGE CODE : 32559    SHEET # 2 OF 2                                                                                                                                |             |
| CHECKED:<br><b>T. Yin</b>                                                                  | DATE:<br><b>06/14/07</b> | CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.                                                                                                                    |             |