



## 0.36" Single Digit Displays

MODEL NO : ELS-315SURWA/S530-A2 ECN : \_\_\_\_\_ Page: 1/5**■ Features :**

- Industrial standard size.
- Low power consumption.
- Categorized for luminous intensity.

**■ Applications:**

- Audio equipment
- Instrument panels
- Digital read out display

**■ Descriptions :**

- The ELS-315 series is a large 9.14mm (0.36")high seven segment display designed for viewing distances up to 7 meters.
- These displays provide excellent reliability in bright ambient light.
- These devices are made with white segments and gray surface.

PART NO	Chip	
	Material	Emitted Color
ELS-315SURWA/S530-A2	AlGaInP	Hyper Red

OFFICE : NO. 25,Lane 76,Sec.3, Chung Yang Rd., Tucheng 236, Taipei, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2267-9936


FAX : 886-2-2267-6244,22676189,22676306

<http://www.everlight.com>

## 0.36" Single Digit Displays

MODEL NO : ELS-315SURWA/S530-A2 ECN : \_\_\_\_\_ Page: 2/5

## ■ Package Dimensions:



## ■ Notes:

1. All dimensions are in millimeters, tolerance is 0.25mm unless otherwise noted.

2. Above specification may be changed without notice.

Supplier will reserve authority on material change for above specification.



# EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : DDS-315-012 REV: 1.1

0.36" Single Digit Displays

MODEL NO : ELS-315SURWA/S530-A2 ECN : \_\_\_\_\_ Page: 4/5

■ Reliability test items and conditions:					
NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85°C 30min ↓ 5 min L : -55°C 30min	50 CYCLE	76 PCS	0/1
3	Thermal Shock	H : +100°C 5min ↓ 10 sec L : -10°C 5min	50 CYCLE	76 PCS	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS	0/1
6	DC Operating Life	IF = 10 mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 PCS	0/1



# EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : DDS-315-012 REV: 1.1

0.36" Single Digit Displays

MODEL NO : ELS-315SURWA/S530-A2 ECN : \_\_\_\_\_ Page: 4/5

■ Reliability test items and conditions:					
NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85°C 30min ↓ 5 min L : -55°C 30min	50 CYCLE	76 PCS	0/1
3	Thermal Shock	H : +100°C 5min ↓ 10 sec L : -10°C 5min	50 CYCLE	76 PCS	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS	0/1
6	DC Operating Life	IF = 10 mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 PCS	0/1

0.36" Single Digit Displays

MODEL NO: ELS-315SURWA/S530-A2

ECN :

Page:

5/5

**■ Typical Electro-Optical Characteristic Curves:**