

PRODUCT MENU

SPRING LOADED DEVICES

[Standard Plungers](#)
[Stubby Plungers](#)
[Ball Plungers](#)
[Push-Fit Plungers](#)
[Ball Buttons & Vlier Wrench](#)
[Quick Release Devices](#)
[Leveling Devices](#)
[Mechanical Components](#)
[RoHS Compliant Products](#)


COMPETITOR PART NO. CROSS REFERENCE

GO




Cage Code 01226


[Distributor Log In](#)
[Distributor Log In](#)

LEARN MORE

[What is SLD?](#)
[Selection Guide](#)
[SLD Basics](#)
[Materials](#)
[Locking Elements](#)
[Detents/Hole Diameter](#)
[Installation](#)


STANDARD PLUNGERS - Posi Hex Metric



Vlier Posi Hex Plungers offer the same features as the standard plunger with one exception: the feature of using a hex wrench to speed up the installation and removal process. These compact units, like the standard plunger, come in two spring force choices in both steel and stainless steel with or without Delrin nose..

Plungers - Posi-Hex Steel/Stainless Steel - Metric								
Part No.		End Force, Lbs.		A Thread 6g-ISO	B mm (in.)	C mm (in.)	øD mm (in.)	HEX mm
Steel	Stainless Steel	Init.	Final					
PHM4	SSPHM4	12.0 (2.7)	32.5 (7.3)	M4 x 0.7	15.9 (.63)	2.4 (.09)	1.8 (.07)	2.0
PHLM4	SSPHLM4	3.1 (0.)	10.2 (2.3)					
PHM5	SSPHM5	12.9 (2.9)	49.4 (11.1)	M5 x 0.8	19.1 (.75)	3.2 (.13)	2.3 (.09)	2.5
PHLM5	SSPHLM5	5.8 (1.3)	12.0 (2.7)					
PHM6	SSPHM6	13.3 (3.0)	57.8 (13.0)	M6 x 1.0	25.4 (1.00)	4.8 (.19)	3.0 (.12)	2.5
PHLM6	SSPHLM6	4.4 (1.0)	17.8 (4.0)					
PHM8	SSPHM8	13.3 (3.0)	66.7 (15)	M8 x 1.25	25.4 (1.00)	4.8 (.19)	3.4 (.14)	2.5
PHLM8	SSPHLM8	6.7 (1.5)	20.0 (4.5)					
PHM10	SSPHM10	24.5 (5.5)	64.5 (14.5)	M10 x 1.5	28.6 (1.13)	4.8 (.19)	4.7 (.19)	4.0
PHLM10	SSPHLM10	12.5 (2.8)	32.0 (7.2)					
PHM12	SSPHM12	29.4 (6.6)	77.4 (17.4)	M12 x 1.75	31.8 (1.25)	6.4 (.25)	6.3 (.25)	6.0
PHLM12	SSPHLM12	12.0 (2.7)	41.4 (9.3)					
PHM16	SSPHM16	46.7 (10.25)	113.4 (25.5)	M16 x 2.0	38.1 (1.5)	7.9 (.31)	79 (.31)	8.0
PHLM16	SSPHLM16	15.6 (3.5)	46.7 (10.5)					

To order with locking element: Add "P" at end of part number.

Plungers - Posi-Hex Steel/Stainless Steel with Delrin Nose- Metric								
Part No.		End Force, Lbs.		A Thread 6g-ISO	B mm (in.)	C mm (in.)	øD mm (in.)	HEX mm
Steel	Stainless Steel	Init.	Final					
DPHM4	DSSPHM4	12.0 (2.7)	32.5 (7.3)	M4 x 0.7	15.9 (.63)	2.4 (.09)	1.8 (.07)	2.0
DPHLM4	DSSPHLM4	3.1 (0.)	10.2 (2.3)					
DPHM5	DSSPHM5	12.9 (2.9)	49.4 (11.1)	M5 x 0.8	19.1 (.75)	3.2 (.13)	2.3 (.09)	2.5
DPHLM5	DSSPHLM5	5.8 (1.3)	12.0 (2.7)					
DPHM6	DSSPHM6	13.3 (3.0)	57.8 (13.0)	M6 x 1.0	25.4 (1.00)	4.8 (.19)	3.0 (.12)	2.5
DPHLM6	DSSPHLM6	4.4 (1.0)	17.8 (4.0)					
DPHM8	DSSPHM8	13.3 (3.0)	66.7 (15)	M8 x 1.25	25.4 (1.00)	4.8 (.19)	3.4 (.14)	2.5
DPHLM8	DSSPHLM8	6.7 (1.5)	20.0 (4.5)					
DPHM10	DSSPHM10	24.5 (5.5)	64.5 (14.5)	M10 x 1.5	28.6 (1.13)	4.8 (.19)	4.7 (.19)	4.0
DPHLM10	DSSPHLM10	12.5 (2.8)	32.0 (7.2)					
DPHM12	DSSPHM12	29.4 (6.6)	77.4 (17.4)	M12 x 1.75	31.8 (1.25)	6.4 (.25)	6.3 (.25)	6.0
DPHLM12	DSSPHLM12	12.0 (2.7)	41.4 (9.3)					

DPHM16	DSSPHM16	46.7 (10.25)	113.4 (25.5)	M16 x 2.0	38.1 (1.5)	7.9 (.31)	79 (.31)	8.0
DPHLM16	DSSPHLM16	15.6 (3.5)	46.7 (10.5)					

To order with locking element: Add "P" at end of part number.

82 South Street • Hopkinton, MA A
Call 1.800.821.1090 ~Fax 1.800.457.2020

