


PRODUCT NUMBER	NO. OF POS	DIM K	DIM J	DIM C	DIM W DIM Z
78211-003 LF	3	7.47	5.08	1.35	0.05
78211-004 LF	4	10.01	7.62	1.35	0.05
78211-005 LF	5	12.55	10.16	1.35	0.05
78211-006 LF	6	15.09	12.70	1.35	0.10
78211-007 LF	7	17.63	15.24	1.35	0.10
78211-008 LF	8	20.17	17.78	1.35	0.10
78211-009 LF	9	22.71	20.32	1.35	0.10
78211-010 LF	10	25.25	22.86	1.35	0.10
78211-011 LF	11	27.79	25.40	1.35	0.15
78211-012 LF	12	30.33	27.94	1.35	0.15
78211-013 LF	13	32.87	30.48	1.35	0.15
78211-014 LF	14	35.41	33.02	1.35	0.15
78211-015 LF	15	37.95	35.56	1.35	0.15
78211-103 LF	3	7.47	5.08	2.54	0.05
78211-105 LF	5	12.55	10.16	2.54	0.05
78211-106 LF	6	15.09	12.70	2.54	0.10

NOTES:

- MOLDING MATERIAL : MODIFIED POLYPHELYNENE
COLOR BLACK, UL 94 V0
- LATCH MUST WITHSTAND 18N MIN PULL OUT FORCE
- STANDARD PACKAGING IN POLYBAGS
- TERMINALS MUST BE CRIMPED PROPERLY FOR SATISFACTORY LATCHING :
 - FOR CRIMPING INSTRUCTIONS, SEE TA-75 AND TA-295
 - FOR TERMINAL APPLICATION SEE TA-531.

PRODUCT SPECIFICATION: BUS-12-067.

- THIS HOUSING IS INTENDED FOR USE WITH MINI PV TERMINAL WITH 22-36 GAUGE WIRE
- RoHS COMPLIANT PRODUCT SPECIFICATIONS :
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.



mat'l. code		surface		tolerance		projection		product family	
10036738		ISO 1302		ISO 406 ISO 1101		mm		BERGCON	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title	
K	V07-0533	HTB	07.08.21	angles	.X ±0.3	scale 5:1		MINI LATCH	
L	B-14321	LMU	13.03.21	linear	.XX ±0.13			HOUSING SR POLARIZED	
M	F-30075	DDE	18.05.03		.XXX ±0.05			dwg no	
				dr	L.MULIN	13.03.21	sheet 1 of 1		size
				enr	L.MULIN	13.03.21	78211		A3
				chr	J.COMPAGNON	13.03.21			
				app	LMU	13.03.21	type		CUSTOMER Drawing
sheet index	revision								
	sheet								