

Features

Regulated Converters

- 8kVDC & 10kVDC Reinforced Isolation
- Industry Standard DIP24 Package
- 3.5W Regulated Output
- Continuous Short Circuit Protection
- Wide Input 2:1
- Medical Approved
- EN, CSA and CB Certificates
- 2 Pinout Options
- Control Pin Option
- Efficiency to 86%

Description

The REC3.5 series uses a reinforced isolation transformer to offer exceptionally high isolation of 8kVDC (4kVAC/1 minute) or 10kVDC (5kVAC/1 minute) making it suitable for HT monitoring circuits, mains power meters, IGBT isolated power supplies and other sophisticated industrial and medical applications. The isolation capacitance of only 20pF makes them also suitable for low leakage applications. The isolation transformer is recognised by CSA as reinforced isolated with a minimum internal clearance of 2.4mm and a minimum internal creepage clearance of 4.6mm. The REC3.5 is available in two industry-standard pinouts (= "/A" or "/C"). Remote on/off control is possible with the /CTRL option (A pinning only) and an optional undervoltage lockout function is also available (= "/X1"). The converters can deliver 140% rated power for short periods of time to cope with applications with large capacitive loads or high start up currents.

Selection Guide

Part Number DIP24	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency (%)	Max. Cap. Load
REC3.5-xx05SRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	5	700	80, 81, 82 77	1000µF
REC3.5-xx09SRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	9	388	81, 82, 83 80	470µF
REC3.5-xx12SRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	12	290	82, 83, 84 82	470µF
REC3.5-xx15SRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	15	233	84, 85, 86 83	330µF
REC3.5-xx24SRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	24	145	83, 84, 85 82	220µF
REC3.5-xx05DRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	±5	±350	80, 81, 82 77	±470µF
REC3.5-xx09DRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	±9	±194	81, 82, 83 80	±220µF
REC3.5-xx12DRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	±12	±145	81, 82, 83 82	±100µF
REC3.5-xx15DRW/R*	9 - 18, 18 - 36, 36 - 75 4.5 - 9	±15	±117	82, 83, 84 80	±100µF

R* = R8 or R10 for 8kVDC or 10kVDC isolation.

2:1 Input

(REC3.5-S_DRW/R8(R10))

xx = 4.5-9Vin = 05

xx = 9-18Vin = 12

xx = 18-36Vin = 24

xx = 36-75Vin = 48

* add suffix "/A" or "/C" for pinning options, see next page for details.

* add suffix "/CTRL" for control pin option (A Pinning only)

* add suffix "/X1" for Undervoltage Lockout

* add suffix -R for Tape and Reel packaging

Ordering Examples:

REC3.5-0512DRW/R8/A/CTRL = 5V Vin, ±12V Vout, 8kVDC isolation, pinout "A", control pin

REC3.5-4805SRW/R10/A = 48V Vin, 5V Vout, 10kVDC isolation, pinout "A"

REC3.5-1212DRW/R8/C/X1 = 12V Vin, ±12V Vout, 8kVDC isolation, pinout "C", UVL


REC3.5-0505SRW/R10/A/CTRL/X1 = 5V Vin, 5V Vout, 10kVDC isolation, pinout "A", control pin, UVL

ECONOLINE

DC/DC-Converter

RECOM

3.5 Watt DIP24 Reinforced Single & Dual Output




C22.2-No. 60950 Certified

C22.2-601.1 Certified

UL Certification Pending

REC3.5/R

Derating-Graph (Ambient Temperature)




Refer to Application Notes

Specifications (measured at $T_A = 25^\circ\text{C}$, nominal input voltage, full load and after warm-up)


Input Voltage Range			2:1	
Output Voltage Accuracy			±2% max.	
Line Regulation	(HL-LL)		±0.3% max.	
Load Regulation	(for output load current change from 20% to 100%)		±0.6% max.	
Input Surge	(1 minute)	5V types	16V max.	
		12V types	25V max.	
		24V types	50V max.	
		48V types	100V max.	
Undervoltage Lockout	(X1 Versions)	5V types	3.5V typ. (±20%)	
		12V types	7V typ. (±20%)	
		24V types	15V typ. (±10%)	
		48V types	32V typ. (±10%)	
Output Ripple and Noise	(0,1µF capacitor on output, 20MHz BW limited)		150mVp-p max.	
Transient Response	(25% step change)		1ms typ.	
Switching Frequency	(Full load and nominal input voltage)		150kHz min. / 500kHz max.	
Input Filter			Pi Network	
Capacitors	All types		MLCC capacitors only	
Minimum Load	(Operation under no load will not damage the converter, but it may not meet all specifications)		10% Full Load	
No Load Power Consumption			400mW max.	
Isolation Voltage	R8 types	(tested for 1 second)	8000VDC min.	
		(rated for 1 minute)	4000VAC min.	
Rated Working Voltage		(long term isolation)	see Application Notes	
Isolation Voltage	R10 types	(tested for 1 second)	10000VDC min.	
		(rated for 1 minute)	5000VAC min.	
Rated Working Voltage		(long term isolation)	see Application Notes	
Isolation Capacitance			20pF typ.	
Isolation Resistance			10 GΩ min.	
Short Circuit Protection	(Max operating temp. = 60°C during short circuit conditions)		Continuous, Auto Restart	
Operating Temperature Range	(free air convection)		-40°C to +85°C (see Graph)	
Case Temperature			105°C max.	
Storage Temperature Range			-55°C to +125°C	
Relative Humidity			95% RH	
Case Material			Non-Conductive Plastic	
Potting Material			Silicone	
Thermal Impedance	Natural convection		20°C/W	
Package Weight			14g	
Packing Quantity			15 pcs per Tube 100 pcs per Reel	
MTBF (+25°C) (+75°C)	} Detailed Information see Application Notes chapter "MTBF"	using MIL-HDBK 217F	1206 x 10³ hours	
		using MIL-HDBK 217F	392x 10³ hours	
EMC (with 470µF//0.1µF capacitors across input)	Conducted Emissions	EN55022	Class A	
	Radiated Emissions	EN55022	Class A	
Reinforced Isolation	Transformer Creepage	/R8 and /R10 Types	4.6 mm min.	
	Transformer Clearance	/R8 and /R10 Types	2.4 mm min.	
	PCB Creepage & Clearance	/R8 and /R10 Types	6.0 mm min.	
	Optocoupler Creepage	/R8 and /R10 Types	6.0 mm min.	
External Creepage and Clearance	Plastic Case	Input <> Output pins	14.2 mm min.	
Certifications	CB Report CSA	Medical Safety	Ref: CA/11158/CSA	IEC60601-1:1988 + A1: 1991 + A2:1995 C22.2 601-1 2nd Ed. UL 60601-1 1st Ed.
		Medical Safety	Report: 2202478	
		General Safety	Report: 2219431	C22.2 No. 60950-1-03 UL 60950-1 1st Ed.
		Recognised as Reinforced Isolation		Supplement to Report: 2219431

Efficiency vs Load




REC3.5-xx05SRW/R*
REC3.5-xx05DRW/R*

Efficiency vs Vin




Efficiency / Load




REC3.5-xx12SRW/R*

Efficiency VS Input Voltage




Efficiency / Load





REC3.5-xx24SRW/R*
REC3.5-xx12DRW/R*

Efficiency VS Input Voltage







"A" Pinning /R8 & /R10



Recommended Footprint Details



CRTL Version only



Pin Connections


Pin #	Single	Dual
1 (option)	CTRL	CTRL
2	-Vin	-Vin
11	NC	-Vout
14	+Vout	+Vout
16	-Vout	Com
22	+Vin	+Vin
23	+Vin	+Vin

NC = No Connection

XX.X ± 0.5 mm
XX.XX ± 0.25 mm



CTRL Option

ON = Open or $0V < V_{ctrl} < 1.2V$
OFF = $2.2V < V_{ctrl} < 12V$





REC3.5/R

"C" Pinning /R8 & /R10



Recommended Footprint Details



Pin Connections

Pin #	Single	Dual
1	+Vin	+Vin
2	+Vin	+Vin
10	NC	Com
11	NC	Com
12	-Vout	NC
13	+Vout	-Vout
15	NC	+Vout
23	-Vin	-Vin
24	-Vin	-Vin

NC = No Connection

XX.X ± 0.5 mm
XX.XX ± 0.25 mm