

# MJD2955 (PNP), MJD3055 (NPN)

## Complementary Power Transistors

### DPAK for Surface Mount Applications

Designed for general purpose amplifier and low speed switching applications.

#### Features

- Lead Formed for Surface Mount Applications in Plastic Sleeves (No Suffix)
- Straight Lead Version in Plastic Sleeves ("–1" Suffix)
- Electrically Similar to MJE2955 and MJE3055
- High Current Gain–Bandwidth Product
- Epoxy Meets UL 94 V–0 @ 0.125 in
- NJV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb–Free and are RoHS Compliant

#### MAXIMUM RATINGS

| Rating                                                                                            | Symbol         | Max           | Unit                     |
|---------------------------------------------------------------------------------------------------|----------------|---------------|--------------------------|
| Collector–Emitter Voltage                                                                         | $V_{CEO}$      | 60            | Vdc                      |
| Collector–Base Voltage                                                                            | $V_{CB}$       | 70            | Vdc                      |
| Emitter–Base Voltage                                                                              | $V_{EB}$       | 5             | Vdc                      |
| Collector Current                                                                                 | $I_C$          | 10            | Adc                      |
| Base Current                                                                                      | $I_B$          | 6             | Adc                      |
| Total Power Dissipation<br>@ $T_C = 25^\circ\text{C}$<br>Derate above $25^\circ\text{C}$          | $P_D^\dagger$  | 20<br>0.16    | W<br>W/ $^\circ\text{C}$ |
| Total Power Dissipation (Note 1)<br>@ $T_A = 25^\circ\text{C}$<br>Derate above $25^\circ\text{C}$ | $P_D$          | 1.75<br>0.014 | W<br>W/ $^\circ\text{C}$ |
| Operating and Storage Junction<br>Temperature Range                                               | $T_J, T_{stg}$ | –55 to +150   | $^\circ\text{C}$         |
| ESD – Human Body Model                                                                            | HBM            | 3B            | V                        |
| ESD – Machine Model                                                                               | MM             | C             | V                        |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

†Safe Area Curves are indicated by Figure 1. Both limits are applicable and must be observed.

1. These ratings are applicable when surface mounted on the minimum pad sizes recommended.





ON Semiconductor®


<http://onsemi.com>

### SILICON POWER TRANSISTORS 10 AMPERES 60 VOLTS, 20 WATTS

#### COMPLEMENTARY




DPAK  
CASE 369C  
STYLE 1




IPAK  
CASE 369D  
STYLE 1

#### MARKING DIAGRAMS



DPAK



IPAK

A = Assembly Location  
Y = Year  
WW = Work Week  
Jxx55 = Device Code  
x = 29 or 30  
G = Pb–Free Package

#### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

## MJD2955 (PNP), MJD3055 (NPN)

### THERMAL CHARACTERISTICS

| Characteristic                                   | Symbol          | Max  | Unit |
|--------------------------------------------------|-----------------|------|------|
| Thermal Resistance, Junction-to-Case             | $R_{\theta JC}$ | 6.25 | °C/W |
| Thermal Resistance, Junction-to-Ambient (Note 2) | $R_{\theta JA}$ | 71.4 | °C/W |

2. These ratings are applicable when surface mounted on the minimum pad sizes recommended.

### ELECTRICAL CHARACTERISTICS ( $T_C = 25^\circ\text{C}$ unless otherwise noted)

| Characteristic | Symbol | Min | Max | Unit |
|----------------|--------|-----|-----|------|
|----------------|--------|-----|-----|------|

#### OFF CHARACTERISTICS

|                                                                                                                                                                                        |                |        |           |                 |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|--------|-----------|-----------------|
| Collector-Emitter Sustaining Voltage (Note 3)<br>( $I_C = 30\text{ mAdc}$ , $I_B = 0$ )                                                                                                | $V_{CEO(sus)}$ | 60     | –         | Vdc             |
| Collector Cutoff Current<br>( $V_{CE} = 30\text{ Vdc}$ , $I_B = 0$ )                                                                                                                   | $I_{CEO}$      | –      | 50        | $\mu\text{Adc}$ |
| Collector Cutoff Current<br>( $V_{CE} = 70\text{ Vdc}$ , $V_{EB(off)} = 1.5\text{ Vdc}$ )<br>( $V_{CE} = 70\text{ Vdc}$ , $V_{EB(off)} = 1.5\text{ Vdc}$ , $T_C = 150^\circ\text{C}$ ) | $I_{CEX}$      | –<br>– | 0.02<br>2 | mAdc            |
| Collector Cutoff Current<br>( $V_{CB} = 70\text{ Vdc}$ , $I_E = 0$ )<br>( $V_{CB} = 70\text{ Vdc}$ , $I_E = 0$ , $T_C = 150^\circ\text{C}$ )                                           | $I_{CBO}$      | –<br>– | 0.02<br>2 | mAdc            |
| Emitter Cutoff Current<br>( $V_{BE} = 5\text{ Vdc}$ , $I_C = 0$ )                                                                                                                      | $I_{EBO}$      | –      | 0.5       | mAdc            |

#### ON CHARACTERISTICS

|                                                                                                                                                          |               |         |          |     |
|----------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|---------|----------|-----|
| DC Current Gain (Note 3)<br>( $I_C = 4\text{ Adc}$ , $V_{CE} = 4\text{ Vdc}$ )<br>( $I_C = 10\text{ Adc}$ , $V_{CE} = 4\text{ Vdc}$ )                    | $h_{FE}$      | 20<br>5 | 100<br>– | –   |
| Collector-Emitter Saturation Voltage (Note 3)<br>( $I_C = 4\text{ Adc}$ , $I_B = 0.4\text{ Adc}$ )<br>( $I_C = 10\text{ Adc}$ , $I_B = 3.3\text{ Adc}$ ) | $V_{CE(sat)}$ | –<br>–  | 1.1<br>8 | Vdc |
| Base-Emitter On Voltage (Note 3)<br>( $I_C = 4\text{ Adc}$ , $V_{CE} = 4\text{ Vdc}$ )                                                                   | $V_{BE(on)}$  | –       | 1.8      | Vdc |

#### DYNAMIC CHARACTERISTICS

|                                                                                                                   |       |   |   |     |
|-------------------------------------------------------------------------------------------------------------------|-------|---|---|-----|
| Current-Gain – Bandwidth Product<br>( $I_C = 500\text{ mAdc}$ , $V_{CE} = 10\text{ Vdc}$ , $f = 500\text{ kHz}$ ) | $f_T$ | 2 | – | MHz |
|-------------------------------------------------------------------------------------------------------------------|-------|---|---|-----|

3. Pulse Test: Pulse Width  $\leq 300\text{ }\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .

# MJD2955 (PNP), MJD3055 (NPN)

## TYPICAL CHARACTERISTICS




Figure 1. Power Derating




Figure 2. DC Current Gain




Figure 3. Turn-On Time




Figure 4. "On" Voltages, MJD3055




Figure 5. Turn-Off Time

## MJD2955 (PNP), MJD3055 (NPN)




Figure 6. "On" Voltages, MJD2955




Figure 7. Switching Time Test Circuit




Figure 8. Thermal Response




Figure 9. Maximum Forward Bias Safe Operating Area

### Forward Bias Safe Operating Area Information

There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate  $I_C - V_{CE}$  limits of the transistor that must be observed for reliable operation; i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 9 is based on  $T_{J(pk)} = 150^\circ\text{C}$ ;  $T_C$  is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided  $T_{J(pk)} \leq 150^\circ\text{C}$ .  $T_{J(pk)}$  may be calculated from the data in Figure 8. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.


## MJD2955 (PNP), MJD3055 (NPN)

### ORDERING INFORMATION

| Device         | Package Type      | Package | Shipping <sup>†</sup> |
|----------------|-------------------|---------|-----------------------|
| MJD2955G       | DPAK<br>(Pb-Free) | 369C    | 75 Units / Rail       |
| MJD2955-1G     | IPAK<br>(Pb-Free) | 369D    | 75 Units / Rail       |
| MJD2955T4G     | DPAK<br>(Pb-Free) | 369C    | 2,500 / Tape & Reel   |
| NJVMJD2955T4G* | DPAK<br>(Pb-Free) | 369C    | 2,500 / Tape & Reel   |
| MJD3055G       | DPAK<br>(Pb-Free) | 369C    | 75 Units / Rail       |
| MJD3055T4G     | DPAK<br>(Pb-Free) | 369C    | 2,500 / Tape & Reel   |
| NJVMJD3055T4G* | DPAK<br>(Pb-Free) | 369C    | 2,500 / Tape & Reel   |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


\*NJV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable



DPAK INSERTION MOUNT  
CASE 369  
ISSUE O

DATE 02 JAN 2000

SCALE 1:1



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  2. CONTROLLING DIMENSION: INCH.

| DIM | INCHES    |       | MILLIMETERS |      |
|-----|-----------|-------|-------------|------|
|     | MIN       | MAX   | MIN         | MAX  |
| A   | 0.235     | 0.250 | 5.97        | 6.35 |
| B   | 0.250     | 0.265 | 6.35        | 6.73 |
| C   | 0.086     | 0.094 | 2.19        | 2.38 |
| D   | 0.027     | 0.035 | 0.69        | 0.88 |
| E   | 0.033     | 0.040 | 0.84        | 1.01 |
| F   | 0.037     | 0.047 | 0.94        | 1.19 |
| G   | 0.090 BSC |       | 2.29 BSC    |      |
| H   | 0.034     | 0.040 | 0.87        | 1.01 |
| J   | 0.018     | 0.023 | 0.46        | 0.58 |
| K   | 0.350     | 0.380 | 8.89        | 9.65 |
| R   | 0.175     | 0.215 | 4.45        | 5.46 |
| S   | 0.050     | 0.090 | 1.27        | 2.28 |
| V   | 0.030     | 0.050 | 0.77        | 1.27 |

STYLE 1:  
PIN 1. BASE  
2. COLLECTOR  
3. EMITTER  
4. COLLECTOR

STYLE 2:  
PIN 1. GATE  
2. DRAIN  
3. SOURCE  
4. DRAIN

STYLE 3:  
PIN 1. ANODE  
2. CATHODE  
3. ANODE  
4. CATHODE


STYLE 4:  
PIN 1. CATHODE  
2. ANODE  
3. GATE  
4. ANODE

STYLE 5:  
PIN 1. GATE  
2. ANODE  
3. CATHODE  
4. ANODE

STYLE 6:  
PIN 1. MT1  
2. MT2  
3. GATE  
4. MT2

|                  |                      |                                                                                                                                                                                     |
|------------------|----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98ASB42319B          | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | DPAK INSERTION MOUNT | PAGE 1 OF 1                                                                                                                                                                         |



onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.




DPAK3 6.10x6.54x2.28, 2.29P  
CASE 369C  
ISSUE H

DATE 15 JUL 2025

SCALE 1:1





| MILLIMETERS |          |       |       |
|-------------|----------|-------|-------|
| DIM         | MIN      | NOM   | MAX   |
| A           | 2.18     | 2.28  | 2.38  |
| A1          | 0.00     | ---   | 0.13  |
| b           | 0.63     | 0.76  | 0.89  |
| b2          | 0.72     | 0.93  | 1.14  |
| b3          | 4.57     | 5.02  | 5.46  |
| c           | 0.46     | 0.54  | 0.61  |
| c2          | 0.46     | 0.54  | 0.61  |
| D           | 5.97     | 6.10  | 6.22  |
| E           | 6.35     | 6.54  | 6.73  |
| e           | 2.29 BSC |       |       |
| H           | 9.40     | 9.91  | 10.41 |
| L           | 1.40     | 10.10 | 1.78  |
| L1          | 2.90 REF |       |       |
| L2          | 0.51 BSC |       |       |
| L3          | 0.89     | ---   | 1.27  |
| L4          | ---      | ---   | 1.01  |
| Z           | 3.93     | ---   | ---   |



NOTES:

1. DIMENSIONING AND TOLERANCING ASME Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS b3, L3, AND Z.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15mm PER SIDE.
5. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
6. DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.
7. OPTIONAL MOLD FEATURE.



RECOMMENDED MOUNTING FOOTPRINT\*

\*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ONSEMI SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.


|                  |                             |                                                                                                                                                                                  |
|------------------|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98AON10527D                 | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | DPAK3 6.10x6.54x2.28, 2.29P | PAGE 1 OF 2                                                                                                                                                                      |

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**DPAK3 6.10x6.54x2.28, 2.29P**  
CASE 369C  
ISSUE H

DATE 15 JUL 2025

**GENERIC  
MARKING DIAGRAM\***



XXXXXX = Device Code  
A = Assembly Location  
L = Wafer Lot  
Y = Year  
WW = Work Week  
G = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

|                                                                       |                                                                       |                                                                  |                                                                            |                                                                   |
|-----------------------------------------------------------------------|-----------------------------------------------------------------------|------------------------------------------------------------------|----------------------------------------------------------------------------|-------------------------------------------------------------------|
| STYLE 1:<br>PIN 1. BASE<br>2. COLLECTOR<br>3. EMITTER<br>4. COLLECTOR | STYLE 2:<br>PIN 1. GATE<br>2. DRAIN<br>3. SOURCE<br>4. DRAIN          | STYLE 3:<br>PIN 1. ANODE<br>2. CATHODE<br>3. ANODE<br>4. CATHODE | STYLE 4:<br>PIN 1. CATHODE<br>2. ANODE<br>3. GATE<br>4. ANODE              | STYLE 5:<br>PIN 1. GATE<br>2. ANODE<br>3. CATHODE<br>4. ANODE     |
| STYLE 6:<br>PIN 1. MT1<br>2. MT2<br>3. GATE<br>4. MT2                 | STYLE 7:<br>PIN 1. GATE<br>2. COLLECTOR<br>3. EMITTER<br>4. COLLECTOR | STYLE 8:<br>PIN 1. N/C<br>2. CATHODE<br>3. ANODE<br>4. CATHODE   | STYLE 9:<br>PIN 1. ANODE<br>2. CATHODE<br>3. RESISTOR ADJUST<br>4. CATHODE | STYLE 10:<br>PIN 1. CATHODE<br>2. ANODE<br>3. CATHODE<br>4. ANODE |

|                  |                             |                                                                                                                                                                                     |
|------------------|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98AON10527D                 | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | DPAK3 6.10x6.54x2.28, 2.29P | PAGE 2 OF 2                                                                                                                                                                         |

**onsemi** and **Onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.



**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)