

F


E

D

C

B

A



P/N

PLATING

67799-0001

1.NICKEL ALLOVER,THICKNESS 0.5 MICROMETER MINIMUM
2.SELECTIVE GOLD 0.1 MICROMETER OVER
PALLADIUM/NICKEL(80/20) 0.5 MICROMETER IN
CONTACT AREA
3.TIN 5.0 MICROMETER MINIMUM IN SOLDER AREA


67799-0011

1.NICKEL ALLOVER,THICKNESS 0.5 MICROMETER MINIMUM
2.SELECTIVE GOLD 0.75 MICROMETER OVER NICKEL
0.5 μ M IN CONTACT AREA
3.TIN 5.0 MICROMETER MINIMUM IN SOLDER AREA

NOTE:

- 1.MATERIAL: HOUSING, HIGH TEMPERATURE POLYMER
TERMINAL, COPPER ALLOY
GROUNDING, COPPER ALLOY
- 2.FINISH: SEE TABLE
- 3.PRODUCT SPECIFICATION: PS-67799-001
- 4.TERMINAL COPLANARITY 0.10MM MAXIMUM
- 5.USE WITH FRAME 67045-0001, 67045-0003, 67771-0001
- 6.PACKAGE: PK-67799-001
- 7.PRODUCT COMPLIANT TO RoHS DIRECTIVE 2002/95/EC
AND ELV 2000/53/EC.

UPDATE DRAWING EC NO: SH2009-0235 DRWN: L SONG9 CHKD: X J SONG APPR: HWANG	QUALITY SYMBOLS ▽=0 ▽C=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	mm	INCH	DRAWN BY BLADE	DATE 2002/06/18	TITLE 50 CKT CF RECEPTACLE SMT TYPE,OFFSET 0.20MM				
				4 PLACES	± ---	± ---	CHECKED BY			DATE		
				3 PLACES	± ---	± ---	WILSON			2002/06/18		
				2 PLACES	± 0.25	± ---	APPROVED BY			DATE		
				1 PLACE	± 0.25	± ---	ERICK			2002/06/18		
			D	REV	ANGULAR ± 3 °		MATERIAL NO.			DOCUMENT NO.		SHEET NO.
					SEE TABLE		SD-67799-001			1 OF 2		
					SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					



Note:

- 1.Material:Black Conductive Polystyrene Alloy.
- 2.All dimensions meet EIA-481-B requirements.
- 3.Packing length per 13" reel : 19.5 Meters
- 4.Component load per 13" reel : 1000 pcs

SEE SHEET 1 EC NO: SH2009-0235 DRWN: SONG CHKD: XJONG APPR: HWANG	DESCRIPTION 2008/10/29 2008/10/29 2008/11/18	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
				mm	INCH	DRAWN BY BLADE	DATE 2002/06/18	TITLE 50 CKT CF RECEPTACLE SMT TYPE,OFFSET 0.20MM					
			4 PLACES	± ---	± ---	CHECKED BY WILSON	DATE 2002/06/18						
			3 PLACES	± ---	± ---								
			2 PLACES	± 0.25	± ---	APPROVED BY ERICK		DATE 2002/06/18	MOLEX INCORPORATED				
			1 PLACE	± 0.25	± ---								
			ANGULAR ± 3 °			MATERIAL NO. SEE SHEET 1		DOCUMENT NO. SD-67799-001		SHEET NO. 2 OF 2			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						