



SERIES**105R & 108R
105 & 108**RoHS
CompliantTraditional
First Quality**Micro i® Chip Inductors**

Actual Size

Military Specifications

Series 105 MIL-PRF-83446 (Reference)

Series 108 MIL-PRF-83446/8 (Reference)

Physical Parameters for Series 105

	Inches	Millimeters
A	0.075 Max.	1.91 Max.
B	0.100 ± 0.010	2.54 ± 0.25
C	0.100 ± 0.010	2.54 ± 0.25
D	0.050 Min.	1.27 Min.
E	0.015 Min. (Typ.)	0.38 Min. (Typ.)
F	0.020 Max. (Typ.)	0.51 Max. (Typ.)

Physical Parameters for Series 108

	Inches	Millimeters
A	0.070 Max.	1.78 Max.
B	0.100 ± 0.010	2.54 ± 0.254
C	0.100 ± 0.010	2.54 ± 0.254
D	0.050 Min.	1.27 Min.
E	0.025 ± 0.005 (Typ.)	0.635 ± 0.13 (Typ.)
F	0.020 Max. (Typ.)	0.51 Max. (Typ.)

Weight Max. (Grams) 0.05**Current Rating at 90°C Ambient** 35°C Rise**Operating Temperature Range** -55°C to +125°C**Maximum Power Dissipation at 90°C** 0.135 W

Mechanical Configuration Units are epoxy encapsulated. Contact areas for reflow soldering are gold plated per MIL-G-45204 Type 1-Grade A. Internal connections are thermal compression bonded.

Packaging Tape & reel (8mm): 7" reel, 2000 pieces max.; 13" reel, 8000 pieces max.

Made in the U.S.A.

MIL DASH # (Reference)
DASH NUMBER*
INDUCTANCE (μH)
TOLERANCE
Q MINIMUM
TEST FREQUENCY (MHz)
SRF MINIMUM (MHz)
DC RESISTANCE MAXIMUM (OHMS)
CURRENT RATING MAXIMUM (mA)

SERIES 105 IRON CORE

-121M		0.12	± 20%	40	25.0	500	0.14	830
-151M		0.15	± 20%	40	25.0	440	0.16	775
-181M		0.18	± 20%	40	25.0	405	0.19	710
-221K		0.22	± 10%	40	25.0	360	0.21	675
-271K		0.27	± 10%	40	25.0	330	0.23	650
-331K		0.33	± 10%	35	25.0	280	0.25	620
-391K		0.39	± 10%	35	25.0	185	0.28	585
-471K		0.47	± 10%	35	25.0	178	0.31	555
-561K		0.56	± 10%	35	25.0	163	0.45	460
-681K		0.68	± 10%	35	25.0	160	0.62	395
-821K		0.82	± 10%	30	25.0	155	0.65	385
-102K		1.0	± 10%	30	25.0	130	0.73	360
-122K		1.2	± 10%	25	7.9	115	1.0	310
-152K		1.5	± 10%	25	7.9	100	1.2	280
-182K		1.8	± 10%	25	7.9	90	1.5	250
-222K		2.2	± 10%	25	7.9	75	1.7	235
-272K		2.7	± 10%	25	7.9	68	2.0	220
-332K		3.3	± 10%	25	7.9	62	2.2	210
-392K		3.9	± 10%	25	7.9	57	2.8	185
-472K		4.7	± 10%	30	7.9	52	3.1	175
-562K		5.6	± 10%	30	7.9	47	3.3	170
-682K		6.8	± 10%	30	7.9	42	3.8	160
-822K		8.2	± 10%	30	7.9	40	5.0	135
-103K		10.0	± 10%	30	7.9	38	5.6	130

M83446/08- (Reference) SERIES 108 IRON CORE

-123K	87	12.0	± 10%	36	2.5	26.0	4.0	79
-153K	88	15.0	± 10%	32	2.5	24.0	4.2	79
-183K	89	18.0	± 10%	32	2.5	21.0	4.4	75
-223K	90	22.0	± 10%	32	2.5	19.0	7.5	57
-273K	91	27.0	± 10%	32	2.5	14.0	8.0	55
-333K	92	33.0	± 10%	30	2.5	12.0	13.0	45
-393K	93	39.0	± 10%	30	2.5	10.0	17.0	38
-473K	94	47.0	± 10%	30	2.5	9.0	19.0	36
-563K	95	56.0	± 10%	30	2.5	8.5	23.0	33
-683K	96	68.0	± 10%	30	2.5	8.2	25.0	32
-823K	97	82.0	± 10%	30	2.5	8.0	28.0	30
-104K	98	100.0	± 10%	30	2.5	7.0	31.0	28

Optional Tolerances: J = 5% H = 3% G = 2% F = 1%

*Complete part # must include series # PLUS the dash #

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

API Delevan:

[105-272K](#) [105-121M](#) [105-121K](#) [105-121J](#) [105-121H](#) [105-121G](#) [105-121F](#) [105-151M](#) [105-151K](#) [105-151J](#) [105-151H](#) [105-151G](#) [105-151F](#) [105-181M](#) [105-181K](#) [105-181J](#) [105-181H](#) [105-181G](#) [105-181F](#) [105-221K](#) [105-221J](#) [105-221H](#) [105-221G](#) [105-221F](#) [105-271K](#) [105-271J](#) [105-271H](#) [105-271G](#) [105-271F](#) [105-331K](#) [105-331J](#) [105-331H](#) [105-331G](#) [105-331F](#) [105-391K](#) [105-391J](#) [105-391H](#) [105-391G](#) [105-391F](#) [105-471K](#) [105-471J](#) [105-471H](#) [105-471G](#) [105-471F](#) [105-561K](#) [105-561J](#) [105-561H](#) [105-561G](#) [105-561F](#) [105-681K](#) [105-681J](#) [105-681H](#) [105-681G](#) [105-681F](#) [105-821K](#) [105-821J](#) [105-821H](#) [105-821G](#) [105-821F](#) [105-102K](#) [105-102J](#) [105-102H](#) [105-102G](#) [105-102F](#) [105-122K](#) [105-122J](#) [105-122H](#) [105-122G](#) [105-122F](#) [105-152K](#) [105-152J](#) [105-152H](#) [105-152G](#) [105-152F](#) [105-182K](#) [105-182J](#) [105-182H](#) [105-182G](#) [105-182F](#) [105-222K](#) [105-222J](#) [105-222H](#) [105-222G](#) [105-222F](#) [105-272J](#) [105-272H](#) [105-272G](#) [105-272F](#) [105-332K](#) [105-332J](#) [105-332H](#) [105-332G](#) [105-332F](#) [105-392K](#) [105-392J](#) [105-392H](#) [105-392G](#) [105-392F](#) [105-472K](#) [105-472J](#)