



RED INDICATES ORIGINAL

DASH NO	MODEL NO	JACK 	TYPE	INCH	MM
-1	AD1W	LIBJ20	BNC	.005	0.13
-2	ADH1W	LIBJ40	TNC	.030	0.76
				.375	9.53
				.471	11.96
				.530	13.46
				2.830	71.88

DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

REVISIONS			1-0348		SH 1C
REV	ECO	DESCRIPTION	DWN	APPROVED	DATE
K	13100	REVISED REDRAWN AND GENERAL UPDATE; .530 MAX DIA OVER KNURL WAS .515 DIM OVER KNURL; 2.830 $\pm$.030 DIMENSION WAS 2.830; ADDED $\pm$.005 TO TOLERANCE BLOCK; DRAWING NUMBER WAS 1000-0348; SEE ECO	DKC		11/11/99



5. VSWR (AVG) 1.065:1 AT 60 MHz
1.11:1 AT 90 MHz

 SEE DASH NO TABLE

3. 75 OHM ADAPTER, LUCENT TYPE PATCH PLUG TO BNC/TNC JACK
2. FINISH: TFS-1A (NICKEL)
1. ALL DIM ARE IN INCHES.

QTY	DESCRIPTION		PART NUMBER		ITEM
TOL UNLESS SPECIFIED .XX $\pm$.XXX $\pm$.005 .XXXX $\pm$ ANGLES $\pm$	TROMPETER ELECTRONICS, INC.		AD1W/ADH1W		
DWN	DKC	10-15-99	MATERIAL	CODE IDENT	DRAWING NO.
CHK		11-10-99		14949	1-0348
ENGR			SCALE 2/1	DATE 10-26-70	SHEET 1C
APPR		11-10-99			

NEXT ASSY