







- NOTES: 1 REFER TO HEADER DRAWING 94898 AND NON-EJECT MECHANISM 92791 FOR ADDITIONAL DIMENSIONS, MATERIAL, AND PLATING INFORMATION.
- 2 REFER TO TA-946 FOR PCB LAYOUT AND PCB KEEP-OUT AREA.
- 3 RECOMMENDED SCREW TORQUE: 1.0 TO 1.5 MAX in.-lbs. (1.2-1.7 cm-kgs).
- 4 PCB SIDE IS AS APPEARS INSTALLED.
- 5 SOLDER TAIL KEY:
R/A = RIGHT ANGLE PIN-THROUGH-HOLE
SMT-STG = STAGGERED SURFACE MOUNT
SMT-IL = SURFACE MOUNT IN-LINE (SINGLE ROW)
- 6 DIM L

4.25±0.1	3.5±0.1	5.0±0.1
OTHERS	36,67	1,17,34,35,51,68




- 7 ADD "H" TO PART NUMBER FOR OPTIONAL HOLD DOWN (4 PER ASSEMBLY)



- 8 ADD "LF" TO PART NUMBER FOR LEAD-FREE TYPE.
- 9 IF LEAD FREE P/N. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
SOLDER TAIL : SMT-IL, SMT-STG CAN RESIST 40 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
SOLDER TAIL : R/A CAN RESIST 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- 10 IF LEAD FREE P/N. THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBED IN GS-22-008
- 11 LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- 12 PRODUCT SPEC:110-263

mat'l. code				surface	tolerance	projection	product family		
ISO 1302				ISO 406	ISO 101		PCMCIA		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
V	ELX-N-17249	HJ	03/20/14	angles	linear	.X±.3	68 POS. 3.3VNON-EJECT		
						.XX±.13	HEADER ASSEMBLY		
						.XXX±.051	scale 1:1		
				dr	R.GRAPE	6/22/98	dwg no		
				enr	D.BRANN	6/22/98	sheet 1 of 4 size		
T	N08-0219	MZ	11/18/08	chr	D.BRANN	6/22/98	84648		
U	ELX-N-15872	HJ	09/18/13	appd	D.BRANN	6/22/98	A4		
sheet				revision	V	V	type		
index				sheet	1	2	CUSTOMER Drawing		

PCB SIDE ④	SOLDER TAIL ⑤	STANDOFF (MM)	Ⓐ EJECT HEADER	Ⓑ EJECT MECHANISM	Ⓒ NOTE ⑥ HOLD DOWN	QTY.	TO MAKE FINAL ASSY PART NUMBER
ABOVE	R/A	NONE	94898-000	92791-001			84648-000
ABOVE	R/A	NONE	94898-000	92791-001	93925-001	4	84648-000H
ABOVE	R/A	2	94898-040	92791-021			84648-020
ABOVE	R/A	2	94898-040	92791-021	93925-002	4	84648-020H
ABOVE	R/A	4	94898-010	92791-041			84648-040
ABOVE	R/A	4	94898-010LF	92791-041			-040LF
ABOVE	R/A	4	94898-010	92791-041	93925-003	4	84648-040H
ABOVE	R/A	4	94898-010LF	92791-041	-003	4	-040HLF
ABOVE	R/A	5	94898-020	92791-051			84648-050
ABOVE	R/A	5	94898-020	92791-051	93925-004	4	84648-050H
ABOVE	R/A	5	94898-021MLF	92791-051M	93925-011	4	84648-050HLF
ABOVE	R/A	5	94898-020	92791-051	63284-104	2	84648-055
ABOVE	R/A	5	94898-021MLF	92791-051M	63284-104	2	84648-055LF
ABOVE	R/A	5	94898-021MLF	92791-053M	63284-104	4	84648-056HLF
ABOVE	R/A	5	SEE TABLE	SEE TABLE	SEE TABLE	4	84648-057HLF
ABOVE	R/A	5	94898-021MLF	92791-051M	63284-011	4	84648-051HLF
ABOVE	SMT-IL	NONE	94898-002	92791-001			84648-002
ABOVE	SMT-IL	NONE	94898-002LF	92791-001			84648-002LF
ABOVE	SMT-IL	NONE	94898-002LF	92791-001A			84648-003LF
ABOVE	SMT-IL	NONE	94898-002LF	92791-001A	93925-001	4	84648-003HLF
ABOVE	R/A	NONE	94898-000LF	92791-001			84648-000LF
ABOVE	R/A	NONE	94898-000LF	92791-001	93925-001	4	84648-000HLF
ABOVE	R/A	2	94898-040LF	92791-021			84648-020LF
ABOVE	R/A	2	94898-040LF	92791-021	93925-002	4	84648-020HLF
ABOVE	R/A	5	94898-020LF	92791-051			84648-050LF
ABOVE	SMT-IL	NONE	94898-002	92791-001	93925-001	4	84648-002H
ABOVE	SMT-STG	NONE	94898-001	92791-001			84648-001
ABOVE	SMT-IL	NONE	94898-002LF	92791-001	-001	4	84648-002HLF
ABOVE	SMT-STG	NONE	94898-001LF	92791-001			84648001LF
BELOW	R/A	NONE	94898-500	92791-001			84648-500
BELOW	R/A	2	94898-540	92791-021			84648-520
BELOW	R/A	4	94898-510	92791-041			84648-540
BELOW	R/A	5	94898-520	92791-051			84648-550
BELOW	R/A	5	94898-520	92791-051	93925-004	4	84648-550H
BELOW	R/A	NONE	94898-500LF	92791-001			84648-500LF
BELOW	R/A	2	94898-540LF	92791-021			84648-520LF
BELOW	R/A	4	94898-510LF	92791-041			84648-540LF
BELOW	R/A	5	94898-520LF	92791-051			84648-550LF
BELOW	R/A	5	94898-520LF	92791-051	93925-004	4	84648550HLF
BELOW	SMT-IL	NONE	94898-502	92791-001			84648-502
BELOW	SMT-IL	NONE	94898-502	92791-001	93925-001	4	84648-502H
BELOW	SMT-STG	NONE	94898-501	92791-001			84648-501
BELOW	SMT-IL	NONE	94898-502LF	92791-001			84648-502LF
BELOW	SMT-IL	NONE	94898-502LF	92791-001	93925-001	4	84648502HLF
BELOW	SMT-STG	NONE	94898-501LF	92791-001			84648-501LF

MOUNTING STYLE
TO P.C.B.





mat'l. code		surface ISO 1302		tolerance ISO 406 ISO 101		projection 101		product family PCMCIA	
ltr		ecn no		dr		date		title	
v								68 POS. 3.3VNON-EJECT HEADER ASSEMBLY	
				angles		linear		MM	
								scale 1:1	
				dr		R.GRAPE		6/22/98	
				enr		D.BRANN		6/22/98	
				chr		D.BRANN		6/22/98	
				appd		D.BRANN		6/22/98	
sheet		revision						FCI	
index		sheet						type CUSTOMER Drawing	

FCI CONFIDENTIAL



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI.
Copyright FCI

PRODUCT NO.
84648-055/055LF



mat'l. code				surface	tolerance	projection	product family PCMCIA		
ltr	ecn no	dr	date	ISO 1302	ISO 406 ISO 101		title		
V				tolerances unless otherwise specified		MM ←→ scale 1:1	68 POS. 3.3VNON-EJECT HEADER ASSEMBLY		
				angles	.X±.3		dwg no		
				linear	.XX±.13		sheet 3 of 4 size		
				±2'	.XXX±.051		84648 A4		
				dr	R.GRAPE 6/22/98		type CUSTOMER Drawing		
				enr	D.BRANN 6/22/98				
				chr	D.BRANN 6/22/98				
				appd	D.BRANN 6/22/98				
sheet index	revision sheet								





FCI CONFIDENTIAL



FCIconnect.com

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI.
Copyright FCI

PRODUCT NO.
84648-056HLF



DETAIL A

mat'l. code				surface	tolerance	projection	product family		
				ISO 1302	ISO 406 ISO 101		PCMCIA		
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM ←→ scale 1:1	title		
V				angles	.X±.3		68 POS. 3.3V NON-EJECT HEADER ASSEMBLY		
				linear	.XX±.13				
				±2'	.XXX±.051		dwg no	sheet 4 of 4	size
				dr	R.GRAPE 6/22/98		84648 A4		
				enr	D.BRANN 6/22/98				
				chr	D.BRANN 6/22/98				
				appd	D.BRANN 6/22/98				
sheet index	revision						type	CUSTOMER	Drawing
	sheet								