

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0461342111

Status:

Obsolete

Description:

Mini-Fit® Plus Crimp Terminal, Male, with Tin (Sn) Plated Brass Contact, 22-24 AWG, Reel

Documents:

Drawing (PDF)

General	
Product Family	Crimp Terminals
Series	46134
Application	Power
Crimp Quality Equipment	Yes
Product Name	Mini-Fit® Plus
Physical	
Durability (mating cycles max)	75
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Reel
Plating min - Mating	2.540µm (100µ")
Plating min - Termination	2.540µm (100µ")
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.20-1.80mm (.047-.071")
Wire Size AWG	22, 24
Wire Size mm²	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-46134-001
Sales Drawing	SD-46134-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

46134Series

Mates With

46083 Mini-Fit Plus™ Female Crimp Terminal

Use With

5559s Single Row Mini-Fit Jr.™ Housing,
30068 Dual Row Mini-Fit® TPA Housing,
5559d Dual Row Mini-Fit Jr.™ Housing,
42475 Dual Row Mini-Fit® MBI Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
FineAdjust for Mini-Fit Jr.™ Crimp Terminals	0639023800
T2 Terminator for Mini-Fit Jr.™ Crimp Terminals	0639123800
FineAdjust™ Applicator	0639002700
T2 Terminator Tooling Die	0639102700
FineAdjust for Mini-Fit Jr.™ Crimp Terminals	0639020200

This document was generated on 05/18/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION