



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT<br>PART NO. | FLANGE<br>THICKNESS              | WEIGHT<br>lbs 10<br>(g) pcs |
|---------------------|----------------------------------|-----------------------------|
| JP4HBC25R- ---      | 0.125 - 0.25<br>(3.18 - 6.35)    | 8.3<br>(3764.82)            |
| JP4HBC50R- ---      | 0.3125 - 0.50<br>(7.94 - 12.7)   |                             |
| JPHBC75R- ---       | 0.5625 - 0.75<br>(14.29 - 19.05) |                             |



#### NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
- HOOK MATERIAL: 33% GLASS FILLED NYLON 6/6  
ANGLE BRACKET MATERIAL: PRE-GALVANIZED STEEL  
RIVET MATERIAL: ALUMINUM  
CLAMP MATERIAL: SPRING STEEL  
NUT MATERIAL: PLATED STEEL
- PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM OF 4.0" (101.6) DIAMETER BUNDLE. MAXIMUM RECOMMENDED STATIC LOAD: 100 lbs.
- PRODUCT INCORPORATES FEATURES ALLOWING USER TO RETAIN CABLE BUNDLES IN J-PRO J-HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
- PRODUCT MARKINGS:  
cULus logo and statement:  
"SUITABLE FOR USE IN AIR HANDLING SPACES IN ACCORDANCE WITH SECTION 300-22 (C) & (D) OF THE NATIONAL ELECTRIC CODE."  
ULC logo and statement:  
"IN ACCORDANCE WITH CAN/ULC S-102.2 IN SINGLE UNITS OR PAIRS, 4 ft (1220mm) MIN. SPACING, FSR=0, SDC=20."

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

CAD FILENAME/LAYERS

G0304DH\_PB\_JP4HBC - -R\_00

**PANDUIT**

CORP.

TINLEY PARK, ILLINOIS

J-PRO J-HOOK WITH 360°  
HAMMER-ON BEAM CLAMP  
(JP4HBC--R- ---)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:

(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)  
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE NONE

DATE 2/10/06

SEE NOTE 2

DRAWING NO.

GB3043DH

DWG  
A  
SIZE

|     |         |     |     |                 |          |     |      |     |  |
|-----|---------|-----|-----|-----------------|----------|-----|------|-----|--|
| R   | 2/10/06 | JAD |     | INITIAL RELEASE | GB3043DH | R   |      |     |  |
| REV | DATE    | BY  | CHK | DESCRIPTION     | ECN      | - R | CUST | SUP |  |