





THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.
© COPYRIGHT - By -


LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
	U2	REVISED PER ECO-11-004587			11MAR11	RK	HMR



SECTION C-C

SECTION A-A

SECTION D-D



WIRE SIZE #20-#24

- 1 GOLD FLASH OVER 0.00127[.000050] NICKEL,.000762[.000030] GOLD ON CONTACT AREA.
- 2 GOLD FLASH OVER 0.00127[.000050] NICKEL,.000381[.000015] GOLD ON CONTACT AREA.
- 3 PREPLATED .00127-.00381 (.000050-.000150) BRIGHT TIN.
- 4 REELED FOR MINI APPLICATOR.
- 5 GOLD PLATING NOT REQUIRED - THIS AREA.
- 6 REELED FOR STANDARD APPLICATOR
- 7 0.000127[.000050] NICKEL OVER ENTIRE CONTACT, 0.000381[.000015] GOLD IN CONTACT AREA.
- 8 SHEARED EDGES ARE PERMITTED TO BE UNPLATED.
- 9 CUT OUTS ON BOX AT MANUFACTURER'S OPTION.
- 10 0.000381[.000015] GOLD IN CONTACT AREA.
0.00254-0.00508[.000100-.000200] BRIGHT TIN-LEAD IN AREA L,
ALL OVER 0.000127[.000050] NICKEL.
- 11 0.000762[.000030] GOLD IN CONTACT AREA.
0.00254-0.00508[.000100-.000200] BRIGHT TIN-LEAD IN AREA L,
ALL OVER 0.000127[.000050] NICKEL.
- 12 OBSOLETE PART NUMBER.
- 13 POINT OF MEASUREMENT FOR PLATING THICKNESS(INSIDE BEAMS).
- 14 0.000127[.000050] NICKEL OVER ENTIRE CONTACT,
0.000762[.000030] GOLD IN CONTACT AREA.
- 15 .000015 GOLD IN CONTACT AREA. .000100-.000200 BRIGHT TIN
IN AREA L, ALL OVER .000050 NICKEL.
- 16 0.000762[.000030] GOLD IN CONTACT AREA.
0.00254-0.00508[.000100-.000200]
MATTE TIN IN AREA L,
ALL OVER 0.000127[.000050] NICKEL.

17 OBSOLETE PARTS: OBSOLETE CIS
STREAMLININGPERD.RENAUD/D.SINISI

LOOSE PIECE	8/16	6-87523-9
REELED	4	6-87523-8
LOOSE PIECE	5/15	2-87523-4
REELED	4	2-87523-3
REELED	6	2-87523-2
REELED	6	2-87523-1
LOOSE PIECE	8/14	1-87523-9
REELED	4	1-87523-8
LOOSE PIECE	8/11	1-87523-6
REELED	4	1-87523-5
LOOSE PIECE	8/10	1-87523-4
REELED	6	1-87523-3
LOOSE PIECE	7/8	1-87523-0
REELED	4	87523-9
REELED	6	87523-8
LOOSE PIECE	2/5	87523-7
LOOSE PIECE	3	87523-6
REELED	4	87523-5
REELED	4	87523-4
LOOSE PIECE	2/5	87523-3
REELED	4	87523-2

OBsolete	LOOSE PIECE	8/16	6-87523-9
OBsolete	REELED	4	6-87523-8
OBsolete	REELED	6	2-87523-4
OBsolete	REELED	4	2-87523-3
OBsolete	REELED	6	2-87523-2
OBsolete	REELED	6	2-87523-1
OBsolete	LOOSE PIECE	8/14	1-87523-9
OBsolete	REELED	4	1-87523-8
OBsolete	LOOSE PIECE	8/11	1-87523-6
OBsolete	REELED	4	1-87523-5
OBsolete	LOOSE PIECE	8/10	1-87523-4
OBsolete	REELED	6	1-87523-3
OBsolete	LOOSE PIECE	7/8	1-87523-0
OBsolete	REELED	4	87523-9
OBsolete	REELED	6	87523-8
OBsolete	LOOSE PIECE	2/5	87523-7
OBsolete	LOOSE PIECE	3	87523-6
OBsolete	REELED	4	87523-5
OBsolete	REELED	4	87523-4
OBsolete	LOOSE PIECE	2/5	87523-3
OBsolete	REELED	4	87523-2

THIS DRAWING IS A CONTROLLED DOCUMENT.			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm [INCHES]		0 PLC	5-5-94
		1 PLC	E.BRANDBERG
		2 PLC	5-5-94
		3 PLC	B. STAUCH
		4 PLC	APVD
		ANGLES	5-5-94
			B. STAUCH
			PRODUCT SPEC
			—
			APPLICATION SPEC
			—
			MATERIAL
			CU-SN-P, ALY 521
		FINISH	SEE TABLE
		ANGLE	—
		WEIGHT	—
		CUSTOMER DRAWING	—
		SCALE	10:1
		RESTRICED TO	—
		SIZE	A2
		CAGE CODE	00779
		DRAWING NO	C-87523

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-87523-9](#) [2-87523-4](#) [87523-6](#)