



For more Information
please call

1-800-Belden1



General Description:

Belden's .050" pitch gray ribbon cable was designed for general purpose electronic interconnect applications. The cable provides reliable mass-termination to standard IDC connectors.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG Stranding	Conductor Material
40	28 7x36	TC - Tinned Copper

Total Number of Conductors: 40

Conductor Spacing Center to Center: .050 +/- .002

Conductor Spacing Outside Center to Outside Center: 1.95 +/- .012

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.254

Insulation Resistance: >10,000 Megaohms

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Overall Cable

Overall Nominal Thickness: .035 +/- .003

Overall Nominal Width: 2.00 +/- .012

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +105°C

Bulk Cable Weight: 77.386 Kg/Km

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL AWM Style:	2651
UL Rating:	105°C, 300 V RMS, VW-1
CSA Specification:	AWM I A 105°C 300 V FT1
CSA Rating:	105°C, 300 V RMS, FT1
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes

EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	VW-1
----------------	------

CSA Flame Test:	FT1
-----------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)**Electrical Characteristics (Overall)****Nom. Characteristic Impedance:**

Description	Impedance (Ohm)
(GS)	150
(GSG)	105

Nom. Inductance:

Description	Inductance (µH/m)
@ 1 MHz (GS)	0.95149
@ 1 MHz (GSG)	0.6562

Nom. Capacitance Conductor to Conductor:

Description	Capacitance (pF/m)
@ 1 kHz (GSG)	59.058
@ 1 MHz (GS)	32.81
@ 1 MHz (GSG)	49.215

Nominal Velocity of Propagation:

Description	VP (%)
	72

Nominal Delay:

Delay (ns/m)
1.40 NS/FT. (GSG)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
68.2 OHMS/1000 FT. MAX.

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
10	9.1868
20	15.7488
30	21.3265
40	27.2323
50	32.1538
60	39.372
70	42.653
80	45.934
90	51.8398
100	55.777

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current

1 Amp per conductor @ 20°C

Dielectric Withstand Voltage: 2,000 V RMS**Typical Unbalanced Crosstalk:**

Description	Pulse Rise Time (NS) (MHz)	Near End % (MHz)	Far End % (MHz)
10 ft. sample length	3	4.8	7
10 ft. sample length	5	3.5	4.7
10 ft. sample length	7	3	3

Notes (Overall)**Notes:** GS=Ground-Signal Mode; GSG=Ground-Signal-Ground Mode**Polarity Identification (Overall)****Polarity Identification:** RED POLARITY STRIPE ON #1 CONDUCTOR**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9L28040 008H100	30 MT	2.540 KG	GRAY		40 #28 STR PVC RIBBON(SMI80)

Revision Number: 2 Revision Date: 09-14-2012

© 2013 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.