






Tous droits strictement réservés. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER  
51530-XX001--  
NOTE: 2



CONNECTOR NOTES:

- HOUSING MATERIAL: UL94 V-0 GLASS FILLED HIGH TEMP. THERMOPLASTIC.  
SIGNAL PIN MATERIAL: COPPER ALLOY.  
POWER CONTACT MATERIAL: COPPER ALLOY.
- PLATING:  
51530-XX001, 51530-XX001LF, PLATING SPEC SEE PRINT: 100064183.
- MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.
- PRODUCT SPECIFICATION GS-12-149.

PCB NOTES:

- ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.
- ALL THROUGH HOLES ARE LOCATED WITH A TRUE POSITION OF 0.004[0.10]
- ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE
- Ø0.079 [2.01] THROUGH HOLES ARE UNPLATED
- Ø0.0453±0.0010 [1.151±0.025] DRILLED HOLES PLATED WITH 0.0003[0.008] MIN SnPb OVER 0.001[0.03] to 0.003[0.08] Cu PLATING TO ACHIEVE A 0.040±0.003 [1.02±.07] HOLE

mat'l code		NOTE 1		tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear	.XX±.01/.X±.3	COPY		www.fciconnect.com	
D					.XXX±.005/.XX±.13	projection		title	
				angles	.XXX±.0020/.XX±.051	INCH/MM		7P + 48S RIGHT ANGLE SOLDER HEADER	
				dr	0° ± 2°	scale		product family	
				enr	M. CLOUSER 06/29/98	1:1		PwrBlade	
				chr	J. BROWN 06/29/98			code	
				appd	J. BROWN 06/29/98			213	
sheet index	revision sheet							sheet	
								2	

cage code 22526 4