







REC.	PART NO.	WIRE RANGE(mm ²)	INSULATION DIA.(mm) (FLR)
MCP 1.5 (B)	1241378	0.2-0.35	1.1-1.4
	1241380	0.5-1.0	1.4-2.1
	1418884	1.5	2.16-2.4




ISO VIEW

WIRE RANGE(mm ³)	INSULATION DIA. (mm)	COLOR	PART NO.
0.35-0.50	1.2-1.6	RED	964971-1
0.50-0.75	1.4-1.9	GREY	963530-1
1.00-1.50	1.9-2.4	YELLOW	964972-1
	DEAD END PLUG	WHITE	963531-1

NOTE ;

- ①. THE COVER OF REC. HSG ASS'Y MUST BE ORDERED SEPARATELY.
2. APPLICABLE REC. CONTACT : SEE TABLE 1.
3. APPLICABLE SINGLE WIRE SEAL : SEE TABLE 2.
4. THE MATING TAB HSG ASS'Y P/N : 1897686-2
5. GENERAL TOLERANCE : ± 0.3 , $\pm 3.0^\circ$
- ⑥. CIRCUIT NO.

4	2005886-1	INNER SEAL	SILICON	ORANGE	1
3	1897691-2	LEVER	PBT-GF20	BLACK	1
2	1897690-2	CAVITY PLUG HSG	PA6-GB20-GF10	BLACK	1
1	1897689-2	REC. HSG	PBT-GF20	BLACK	1
NO.	PART NO.	DESCRIPTION	MATERIAL	COLOR	Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SJ CHOI	 TE Connectivity			
DIMENSIONS:		CHK KT LIM				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED 0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±	APVD HG CHO	NAME			
		PRODUCT SPEC	MCP1.5 SEALED 18P REC. HSG ASS'Y			
		APPLICATION SPEC	-			
		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL		FINISH	A300779 C=1897688			-
-	-	CUSTOMER DRAWING				
-	-	SCALE 1:1			SHEET 1 OF 1	REV B