



	1	2	3	4	5	6	7																							
A	Material Item a Male contact pin: Copper Tin plated Item b Terminal (housing): Thermoplastic (UL94V-0) , GREEN Electrical cULus/VDE Voltage rating: 300V/300V Current rating: 8A/10A Withstanding Voltage: 1.6KV/2.5KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval:  							A																						
B								B																						
C								C																						
D								D																						
E	 RECOMMENDER PCB LAYOUT							E																						
F	DIMENSION<table><tr><td>L</td><td>(N-1)x3.5+4.9</td></tr><tr><td>P</td><td>(N-1)x3.5</td></tr></table> N=Number of poles <table><tr><th>Poles</th><th colspan="2">Tolerance</th></tr><tr><td></td><th>DIM L</th><th>DIM P</th></tr><tr><td>2p-6p</td><td>±0.15</td><td>±0.15</td></tr><tr><td>7p-12p</td><td>±0.20</td><td>±0.20</td></tr><tr><td>13p-18p</td><td>±0.25</td><td>±0.25</td></tr><tr><td>19p-24p</td><td>±0.30</td><td>±0.30</td></tr></table>							L	(N-1)x3.5+4.9	P	(N-1)x3.5	Poles	Tolerance			DIM L	DIM P	2p-6p	±0.15	±0.15	7p-12p	±0.20	±0.20	13p-18p	±0.25	±0.25	19p-24p	±0.30	±0.30	F
L	(N-1)x3.5+4.9																													
P	(N-1)x3.5																													
Poles	Tolerance																													
	DIM L	DIM P																												
2p-6p	±0.15	±0.15																												
7p-12p	±0.20	±0.20																												
13p-18p	±0.25	±0.25																												
19p-24p	±0.30	±0.30																												
G	Scale 1:1 TOLERANCE<table><tr><td>X.</td><td>±0.50</td></tr><tr><td>X.X</td><td>±0.30</td></tr><tr><td>X.XX</td><td>±0.10</td></tr></table> DIM TOL X.° ±1° Angle TOL Id. Modification Date Name							X.	±0.50	X.X	±0.30	X.XX	±0.10	G																
X.	±0.50																													
X.X	±0.30																													
X.XX	±0.10																													
H	RoHS compliant  File No.: E349947  ASSMANN WSW-No. A-TB350-VKxx Drawing-No. ASS 4118 CO Replace rev01 Sheet							H																						
	1	2	3	4	5	6	7																							