




THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20	
© COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H6	REVISED PER ECO-11-005027	14MAR2011	RK	HMR

TEST FACILITY

INTERLOCKING FEATURE

CLAMPING SCREW

0.50±0.05
TYP

282841-3 AS SHOWN
PRELIMINARY

A

15.20

3.5±0.3
TYP

2.54 REF

1.0±0.1
TYP

5.08±0.05
TYP

5.08

9.00

0.80±0.05
TYP

Ø 1.4^{+0.1}₀

Ø 0.1


RECOMMENDED PC BOARD LAYOUT
SCALE 5:1

DETAIL C	PRELIMINARY	-	SEE SHEET 2	GREEN	15.24	3	4-282841-0
DETAIL B	PRELIMINARY	-	-	GREEN	25.40	5	3-282841-9
	PRELIMINARY	-	-	GREEN	20.32	4	3-282841-8
	PRELIMINARY	STAINLESS STEEL	-	GREEN	40.64	8	3-282841-7
	PRELIMINARY	STAINLESS STEEL	-	GREEN	20.32	4	3-282841-6
	PRELIMINARY	STAINLESS STEEL	-	GREEN	15.24	3	3-282841-5
	PRELIMINARY	STAINLESS STEEL	-	GREEN	10.16	2	3-282841-4
			SEE SHEET 2	GREEN	45.72	9	3-282841-3
			SEE SHEET 2	GREEN	66.04	13	3-282841-2
			SEE SHEET 2	GREEN	20.32	4	3-282841-1
			SEE SHEET 2	GREEN	60.96	12	3-282841-0
			-	BLACK	127.0	25	2-282841-9
			-	GREEN	127.0	25	2-282841-8
			-	GREEN	121.92	24	2-282841-7
			-	GREEN	116.84	23	2-282841-6
			-	GREEN	111.76	22	2-282841-5
			-	GREEN	106.68	21	2-282841-4
			-	GREEN	101.60	20	2-282841-3
			-	GREEN	96.52	19	2-282841-2
			-	GREEN	91.44	18	2-282841-1
			-	GREEN	86.36	17	2-282841-0
			-	GREEN	81.28	16	1-282841-9
			-	GREEN	76.20	15	1-282841-8
			-	GREEN	71.12	14	1-282841-7
			-	GREEN	66.04	13	1-282841-6
			SEE SHEET 2	GREEN	40.64	8	1-282841-5
			SEE SHEET 2	GREEN	35.56	7	1-282841-4
			-	BLACK	35.56	7	1-282841-3
			-	GREEN	60.96	12	1-282841-2
			-	GREEN	55.88	11	1-282841-1
			-	GREEN	50.80	10	1-282841-0
			-	GREEN	45.72	9	282841-9
			-	GREEN	40.64	8	282841-8
			-	GREEN	35.56	7	282841-7
			-	GREEN	30.48	6	282841-6
			-	GREEN	25.40	5	282841-5
			-	GREEN	20.32	4	282841-4
			-	GREEN	15.24	3	282841-3
			-	GREEN	10.16	2	282841-2
	CLAMPING SCREW	MARKING	COLOR	A	NO OF POSN	PART NUMBER	


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	26 JAN 2001	TE Connectivity							
		CHK	S. WELDON								
		APVD	D. BIEVENOUR								
		APVD	D. BIEVENOUR								
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
mm		0 PLC ±0		TERMINAL BLOCK PCB MOUNT W/INTERLOCK, 5.08mm PITCH							
		1 PLC ±.3									
		2 PLC ±.25									
		3 PLC ±0									
		4 PLC ±0		SIZE							
		ANGLES ±2°		CAGE CODE							
MATERIAL		FINISH		DRAWING NO							
				RESTRICTED TO							
				A200779C-282841							
				SCALE							
				4:1							
				SHEET							
				1 OF 2							
				REV							
				H6							

1471-9 (3/11)


LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-




3-282841-1 AS SHOWN 




1-282841-4 AS SHOWN




1-282841-5 AS SHOWN 




3-282841-3 AS SHOWN 



3-282841-0 AS SHOWN 



4-282841-0 AS SHOWN 



3-282841-2 AS SHOWN 

1. MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: SEE TABLE.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2. SUITABLE FOR 1,6-2,4mm. PCB THICKNESS.

3. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.

4. WIRE SIZE RANGE: 12-30 AWG



5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE No E60677.

6. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.

7. NOT CUMULATIVE TOLERANCE.

8. INK MARKING : BLACK COLOR.

9. BUCHANAN LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL, WHERE SPACE PERMITS.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26 JAN 2001 S. WELDON CHK 26 JAN 2001 D. BIEVENOUR APVD 26 JAN 2001 D. BIEVENOUR		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0 1 PLC $\pm .3$ 2 PLC $\pm .25$ 3 PLC ± 0 4 PLC ± 0 ANGLES $\pm 2^\circ$ FINISH		NAME TERMINAL BLOCK PCB MOUNT W/INTERLOCK, 5.08mm PITCH	
		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE CAGE CODE DRAWING NO A2 00779 C-282841	
MATERIAL -		CUSTOMER DRAWING		RESTRICTED TO - SCALE 3:1 SHEET 2 OF 2 REV H6	