


DRAWING MADE IN AMERICAN PROJECTION

LOC
GPRINT DIST
14

©1963 BY AMP INCORPORATED. ALL
RIGHTS RESERVED. AMP PRODUCTS
COVERED BY PATENTS AND/OR
PATENTS PENDING.

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
A	REDRAWN & REVISED	PC-556 1-5-70	JT
B	REV G-4680	TMS 5-6-88	JT



TONGUE MATERIAL THICKNESS = .040 $\pm$.003
FOR .377 MAX WIRE INS. DIA

1	WIRE TERMINAL	322154	BODY: COPPER (99.95%) TIN PLATE (0.05%) INSULATION PVC COLOR: RED METALLIC SLEEVE COPPER (99.95%) METALLIC BAND: STEEL QQ-S-228 (ASTM A292) MATERIAL & FINISH
QTY	DESCRIPTION	PART NO	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON DECIMALS: .008 ANGLES: 5°			CONTRACT NO. DR. <i>Wayne Miller</i> 11-18-69 CHK. <i>W. E. ...</i> 1-5-70 APPD. <i>Swabach</i> 1-7-70 REL. <i>M. E. ...</i> 1-8-70 DSGN APPD. <i>...</i> OTHER APPD. <i>...</i>
MATERIAL			AMP INCORPORATED HARRISBURG, PENNSYLVANIA NAME: WIRE TERMINAL AMPLI-BOND-RING TONGUE WIRE SIZE: 8
SEE TABLE			SIZE: A CODE IDENT NO: 00779 NUMBER: 322154
			SCALE: NTS SHEET 1 OF 1