






RECOMMENDED HOLE LAYOUT

8	7	6	1,2,39,40	1,2,39,40	3.984	3.900	39	80	7-104354-0	
	7	6	1,2,29,30	1,2,29,30	2.984	2.900	29	60	6-104354-9	
	7	6	1,2,24,25	1,2,24,25	2.484	2.400	24	50	6-104354-8	
	7	6	1,2,19,20	1,2,19,20	1.984	1.900	19	40	6-104354-7	
	7	6	1,2,16,17	1,2,16,17	1.684	1.600	16	34	6-104354-6	
	7	6	1,2,14,15	1,2,14,15	1.484	1.400	14	30	6-104354-5	
	7	6	1,2,13,14	1,2,13,14	1.384	1.300	13	28	6-104354-4	
	7	6	1,2,12,13	1,2,12,13	1.284	1.200	12	26	6-104354-3	
	7	6	1,2,11,12	1,2,11,12	1.184	1.100	11	24	6-104354-2	
	7	6	1,2,10,11	1,2,10,11	1.084	1.000	10	22	6-104354-1	
	7	6	1,2,9,10	1,2,9,10	.984	.900	9	20	6-104354-0	
	7	6	1,2,8,9	1,2,8,9	.884	.800	8	18	5-104354-9	
	7	6	1,2,7,8	1,2,7,8	.784	.700	7	16	5-104354-8	
	7	6	1,2,6,7	1,2,6,7	.684	.600	6	14	5-104354-7	
8	6	5	1,2,5,6	1,2,5,6	.584	.500	5	12	5-104354-6	
	7	6	1,2,4,5	1,2,4,5	.484	.400	4	10	5-104354-5	
	7	6	1,2,3,4	1,2,3,4	.384	.300	3	8	5-104354-4	
	7	6	1,2,3	1,2,3	.284	.200	2	6	5-104354-3	
	7	6	1,2	1,2	.184	.100	1	4	5-104354-2	
	5		1,2,39,40	1,2,39,40	3.984	3.900	39	80	2-104354-0	
	5		1,2,29,30	1,2,29,30	2.984	2.900	29	60	1-104354-9	
	5		1,2,24,25	1,2,24,25	2.484	2.400	24	50	1-104354-8	
	5		1,2,19,20	1,2,19,20	1.984	1.900	19	40	1-104354-7	
	5		1,2,16,17	1,2,16,17	1.684	1.600	16	34	1-104354-6	
	5		1,2,14,15	1,2,14,15	1.484	1.400	14	30	1-104354-5	
	5		1,2,13,14	1,2,13,14	1.384	1.300	13	28	1-104354-4	
	5		1,2,12,13	1,2,12,13	1.284	1.200	12	26	1-104354-3	
	5		1,2,11,12	1,2,11,12	1.184	1.100	11	24	1-104354-2	
5		1,2,10,11	1,2,10,11	1.084	1.000	10	22	1-104354-1		
8	5		1,2,9,10	1,2,9,10	.984	.900	9	20	1-104354-0	
	5		1,2,8,9	1,2,8,9	.884	.800	8	18	104354-9	
	5		1,2,7,8	1,2,7,8	.784	.700	7	16	104354-8	
	5		1,2,6,7	1,2,6,7	.684	.600	6	14	104354-7	
	5		1,2,5,6	1,2,5,6	.584	.500	5	12	104354-6	
	5		1,2,4,5	1,2,4,5	.484	.400	4	10	104354-5	
	5		1,2,3,4	1,2,3,4	.384	.300	3	8	104354-4	
	5		1,2,3	1,2,3	.284	.200	2	6	104354-3	
	5		1,2	1,2	.184	.100	1	4	104354-2	
	5		1	1	.084	—	—	2	104354-1	
	8	REMARKS	PLATING	ROW N	ROW M	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER
		HOLD-DOWN POST CONFIG LOCATION								

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 2-4-88 M. PASTAL OK R. FEJDT APPROVED R. FEJDT 2-9-88		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.005 4 PLC ± ANGLES ± FINISH		NAME HEADER ASSEMBLY, MOD II, BREAKAWAY, RIGHT ANGLE, DOUBLE, ROW, .100X.100 CL, .025 SQ POSITS WITH LOW-DOWN CONFIGURATIONS	
		PRODUCT SPEC APPLICATION SPEC		SIZE GAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL: HOUSING: NAME: REWORKED THERMOPLASTIC POLYESTER: BLACK COLOR: COPPER ALLOY		WEIGHT —		A1 00779 C 104354	
SEE TABLE		CUSTOMER DRAWING		SCALE: 4:1 SHEET 1 of 1 REV H	