




LOC	DIST	REVISIONS					
AA	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	ECO-07-010988	15MAY2007	LAM	JW
			D	ECO-08-000960	15JAN2008	LAM	JW
			E	ECO-08-028011	11NOV2008	JY	SY
			E1	REVISED PER ECO-10-000445	11JAN10	KK	AEG

1. MATERIAL:
HOUSING - PBT POLYESTER, BLACK, UL 94V-0
- TERMINALS - 0.33 THICK PHOS BRONZE PLATED WITH 1.27µm MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 2µm MINIMUM THICK MATTE TIN IN ACTION PIN COMPLIANT PIN TERMINAL AREA OVER 1.27µm MINIMUM THICK NICKEL UNDERPLATE
- SHIELD - 0.25 THICK COPPER ALLOY PLATED WITH 2.03µm MINIMUM BRIGHT TIN OVER 1.27µm MINIMUM NICKEL
- GROUNDING CLIP - 2.03 µm MIN MATTE TIN OVER COPPER, PRE-PLATED COPPER ALLOY
- LED - DIFUSED EPOXY LENS 2.29 µm SILVER OVER NICKEL PRE-PLATED CARBON STEEL LEADS
- ACTION PIN - COMPLIANT PIN CONTACTS 0.3 THICK BRASS PLATED WITH 2-4µm BRIGHT TIN.
2. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3. DRILLED HOLE DIA = 1.020±0.025
COPPER THICKNESS = 0.025±0.075
TIN-LEAD THICKNESS = .008
4. DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
5. DATE CODE LOCATED ON REAR OF PART APPROXIMATELY AS SHOWN
6. CONTACTS ARE NOT INTENDED TO BE ALIGNED WITH EACH OTHER
7. **OBsolete PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI**


6368168-1 SHOWN
SHEET 1



RECOMMENDED PANEL CUT-OUT



PC BOARD LAYOUT
(COMPONENT SIDE)





OBsolete

GREEN	GREEN	YELLOW	YELLOW	YES	WITH LED PORTS	6368168-6
GREEN	GREEN	GREEN	GREEN	YES	WITH LED PORTS	6368168-5
YELLOW	YELLOW	GREEN	GREEN	YES	WITH LED PORTS	6368168-4
N/A	N/A	N/A	N/A	YES	WITHOUT LED PORTS	6368168-2
N/A	N/A	N/A	N/A	NO	WITHOUT LED PORTS	6368168-1
LED #4	LED #3	LED #2	LED #1	GROUNDING CLIP	SHIELD STYLE	PART NUMBER



DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		TYCO Electronics	
mm		0 PLC ±		A. FERNANDEZ		TYCO Electronics Corporation	
0 PLC ±		1 PLC ±		J. WESTMAN		Harrisburg, PA 17105-3608	
3 PLC ±		4 PLC ±		S. FLICKINGER		NAME	
MATERIAL		FINISH		PRODUCT SPEC		STACKED MODULAR JACK ASSEMBLY,	
SEE NOTE 1		SEE NOTE 1		APPLICATION SPEC		2X1, 8 POSITION, SHIELDED	
SCALE		WEIGHT		114-2160		PANEL GROUND, OFFSET, CAT 5	
3:1		CAGE CODE		114-2160		SIZE	
SHEET		DRAWING NO		A1 00779		RESTRICTED TO	
OF 2		REV		E1			

LOC		DIST		REVISIONS					
AA		00		REV	LYR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-



6368168-6 SHOWN
SHEET 2

SHIELD WITH LED CUTOUTS AND
STANDARD PANEL GROUNDS



THE INFORMATION CONTAINED HEREIN IS UNCLASSIFIED EXCEPT WHERE SHOWN OTHERWISE. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION AND IS NOT TO BE RELEASED TO THE PUBLIC OR TO ANY OTHER ORGANIZATION WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS CORPORATION.		DWN A. FERNANDEZ-DOCK 28 JUL 2005	TYCO Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK J. WESTMAN 28 JUL 2005	NAME STACKED MODULAR JACK ASSEMBLY, 2X1, 8 POSITION, SHIELDED PANEL GROUND, OFFSET, CAT 5	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. FLICKINGER 28 JUL 2005	SIZE CAGE CODE DRAWING NO.	
0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ±		PRODUCT SPEC 108-1854 APPLICATION SPEC 114-2160	RESTRICTED TO A1 00779 C-6368168	
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1	CUSTOMER DRAWING	
		SCALE 3:1	SHEET 2 OF 2	
			REV E1	