





UNCONTROLLED DOCUMENT



NOTES:

1. ANODE
2. CATHODE
3. EMITTER
4. COLLECTOR



ELECTRO-OPTICAL CHARACTERISTICS (Ta=25°C)

	PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
I	FORWARD VOLTAGE	V _F	I _F =20mA	—	1.2	1.4	V
	PEAK FORWARD VOLTAGE	V _{FM}	I _{FM} =0.5A	—	—	3.5	V
	REVERSE CURRENT	I _R	V _R =4V	—	—	10	μA
	TERMINAL CAPACITANCE	C _t	V=0, f=1kHz	—	30	—	pF
O	COLLECTOR DARK CURRENT	I _{CE0}	V _{CE} =20V	—	—	10 ⁻⁷	A
T	CURRENT TRANSFER RATIO	CRT	I _F =2mA, V _{CE} =5V	50	—	600	%
	COLLECTOR-EMITTER SATURATION VOLTAGE	V _{CE(sat)}	I _F =20mA, I _C =1mA	—	0.1	0.3	V
	ISOLATION RESISTANCE	R _{iso}	DC500V	5x10 ¹⁰	10 ¹¹	—	ohm
	FLOATING CAPACITANCE	C _f	V=0, f=1MHz	—	0.6	1.0	pF
	CUT-OFF FREQUENCY	f _c	V _{CE} =5V, I _C =2mA, R _L =100ohm	—	80	—	kHz
	RESPONSE TIME (RISE)	t _r	V _{CE} =5V, I _C =2mA, R _L =100ohm	—	5	20	μS
	RESPONSE TIME (FALL)	t _f	V _{CE} =5V, I _C =2mA, R _L =100ohm	—	4	20	μS

I=INPUT, O=OUTPUT, T=TRANSFER CHARACTERISTICS.

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN=+DECIMAL PRECISION MAX.=+0.00 -0.00 -DECIMAL PRECISION

PART NUMBER
OCP-PCT114/X

REV.

C

REV.	E.C.N. NUMBER AND REVISION COMMENTS	DATE
A	E.C.N. #10BRDR. & #10776.	8.16.01
B	E.C.N. #11148.	5.16.07
C	E.C.N. #11534.	10.03.08

PART NUMBER TABLE

PART=	CTR (%)
/A	60 TO 160
/B	130 TO 260
/C	200 TO 400
/D	300 TO 600
/E	50 TO 600

ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

	PARAMETER	SYMBOL	MAX	UNITS
I	FORWARD CURRENT	I _F	50	mA
	PEAK FORWARD CURRENT	I _{FM}	1	A
	REVERSE VOLTAGE	V _R	6	V
	POWER DISSIPATION	P _D	70	mW
O	COLLECTOR-EMITTER VOLTAGE	V _{CE0}	60	V
	EMITTER-COLLECTOR VOLTAGE	V _{EC0}	6	V
	COLLECTOR CURRENT	I _C	50	mA
	COLLECTOR POWER DISSIPATION	P _C	150	mW
	TOTAL POWER DISSIPATION	P _{tot}	200	mW
	ISOLATION VOLTAGE 1 MIN.	V _{iso}	5000	V _{RMS}
	OPERATING TEMPERATURE	T _{opr}	-30 TO +100	°C
	STORAGE TEMPERATURE	T _{stg}	-55 TO +125	°C
	SOLDERING TEMPERATURE	T _{sol}	+260	°C
	2.0mm FROM BODY		10 SEC. MAX	

I=INPUT, O=OUTPUT.

UNCONTROLLED DOCUMENT

REV.

C

PART NUMBER

OCP-PCT114/X

CONFIDENTIAL INFORMATION

THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

RELIABILITY NOTE

OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.



290 E. HELEN ROAD
PALATINE, IL 60067-6976
PHONE: +1.847.359.2790
US WEB: www.lumex.com
TW WEB: www.lumex.com.tw

DRAWN BY:	CHECKED BY:	APPROVED BY:	DATE: 9.29.99
JC			PAGE: 1 OF 1
			SCALE: N/A

FOUR PIN DIP SINGLE CHANNEL PHOTOCOUPLER,
TRANSISTOR OUTPUT, NO EXTERNAL BASE CONNECTION.