






MCNDI Series

DIL Switches



NDI



Features:

- Single pole single throw DIL switches.
- Splay terminals allow for automatic insertion by IC insertion machine.
- Insert moulding of terminals and ultrasonic welding improve flux proofness and enable flux washing in whole by top tape sealing.
- NDI series (raised actuator) available for different purposes.
- Double contacts offers high reliability.
- Vapour phase solderable, IR-reflow solderable.
- Terminal plating by gold give excellent results when soldering.

Terminal plating : Tin/lead available too.
Lead Spacing : 7.62 x 2.54.

Materials:

Base and cover : High temperature thermoplastic.
Colour : Black.
Actuator : Nylon thermoplastic.
Colour : White.
Contact : Alloy copper.
Contact plating : Gold plated over nickel.
Terminal plating : Gold. (or Tin/Lead available).
Tape plating : Kapton.
Life expectancy : 2000ops.

It is recommended to solder switches in the 'off' factory supplied position.

Specifications:

Mechanical:

Mechanical life : 2000 operations per switch.
Operation force : 1000gf maximum.
Operating temperature : -20°C to +85°C.
Storage temperature : -40°C to +85°C.
Vibration test : MIL-STD-202F Method 201A.
Frequency : 10 - 55 - 10Hz/1 minute.
Directions : X, Y, Z three mutually perpendicular directions.
Time : 2 hours each direction.
High reliability.
Shock test : MIL-STD-202F Method 213B.
Condition A.
Gravity : 50G (peak value), 11 milliseconds.
Direction and times : 6 sides and 3 times in each direction.
High reliability.




MCNDI Series

DIL Switches



Dimensions

NDI




Schematic (Typical)



02, 04, 06, 08 and 10 position available

Terminal Type

NDI- S



Specifications:

Electrical:

Electrical life	: 2000 operations minimum per switch 24V dc, 25mA.
Non-switching rating	: 100mA, 50V dc.
Switching rating	: 25mA 24V dc.
Contact resistance	: [a] 50mΩ maximum at initial. [b] 100mΩ maximum after life test.
Capacitance	: 5pF maximum.
Operating temperature	: -20°C to +70°C.
Insulation resistance	: 100MΩ minimum at 500V dc.
Dielectric strength	: 500V ac per 1 minute.
Capacitance	: 5pF maximum
Circuit	: Single pole single throw.

Soldering and Cleaning Process:

For best results, please follow these recommendation:

Keep all switch contacts in their "OFF" position for all operations.


Wave soldering : Recommended solder temperature at 500°F (260°C) maximum, 5 seconds. For through hole type.

Hand soldering : Use a soldering iron of 30 watts, controlled at 608°F (320°C) approximately 2 seconds while applying solder.



MCNDI Series

DIL Switches




Reflow temperature profile.
 Care should be exercised so that flux from the upper part of the printed circuit board does not adhere to the switch.
 Do not clean the switch body except with top tape sealed type, which can only spray of cleaning method from top s/w.

Specifications Table

Number of Positions	Dimension A	Dimension B	Part Number
02	6.02 (0.237)	2.54 (0.100)	MCNDI-02S
04	11.10 (0.437)	7.62 (0.300)	MCNDI-04S
06	16.18 (0.637)	12.70 (0.500)	MCNDI-06S
08	21.26 (0.837)	17.78 (0.700)	MCNDI-08S
10	26.34 (1.037)	22.86 (0.900)	MCNDI-10S

Dimensions : Millimetres (Inches)

Part Number Explanation



- Insertable Type** : NDI = Machine insertable Type DIP switch.
- Number of Positions** : 02, 04, 06, 08 and 10.
- Shape of Terminal** : S = Splay Terminal.



MCNDI Series

DIL Switches



Notes:

International Sales Offices:



AUSTRALIA – Farnell InOne
Tel No: ++ 61 2 9645 8888
Fax No: ++ 61 2 9644 7898



FINLAND – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



NETHERLANDS – Farnell InOne
Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND – Farnell InOne
Tel No: ++ 41 1 204 64 64
Fax No: ++ 41 1 204 64 54



AUSTRIA – Farnell InOne
Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE – Farnell InOne
Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



NEW ZEALAND – Farnell InOne
Tel No: ++ 64 9 357 0646
Fax No: ++ 64 9 357 0656



UK – Farnell InOne
Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



BELGIUM – Farnell InOne
Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY – Farnell InOne
Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NORWAY – Farnell InOne
Tel No: ++ 45 44 53 66 66
Fax No: ++ 45 44 53 66 02



UK – BuckHickman InOne
++ 44 8450 510 150
++ 44 8450 510 130



BRAZIL – Farnell-Newark InOne
Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG – Farnell-Newark InOne
Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



PORTUGAL – Farnell InOne
Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



UK – CPC
++ 44 8701 202 530
++ 44 8701 202 531



CHINA – Farnell-Newark InOne
Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



IRELAND – Farnell InOne
Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



SINGAPORE – Farnell-Newark InOne
Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300



EXPORT – Farnell InOne
Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



DENMARK – Farnell InOne
Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



ITALY – Farnell InOne
Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN – Farnell InOne
Tel No: ++ 34 93 475 8805
Fax No: ++ 34 93 474 5107



ESTONIA – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



MALAYSIA – Farnell-Newark InOne
Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN – Farnell InOne
Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62

<http://www.farnellinone.com>

<http://www.buckhickmaninone.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2004.

