



THIS DRAWING IS UNPUBLISHED.  
RELEASED FOR PUBLICATION 20  
BY -  
ALL RIGHTS RESERVED.  
© COPYRIGHT 20 BY -

## REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECO-II-005030	12MAR2011	RK	HMR
	C3	REVISED PER ECO-13-016087	14OCT2013	DD	MB



1 FINISH: PLATED 0.00076 MIN THICK GOLD IN MATING AREA WITH 0.0025 MIN THICK TIN IN WIRE CRIMP AREA, ALL OVER 0.002 MIN THICK NICKEL.

2 FINISH: PLATED 0.00076 MIN THICK GOLD IN MATING AREA, PLATED 0.00038 MIN THICK GOLD IN SHUNT CONTACT PLATING AREA WITH 0.0025 MIN THICK TIN IN WIRE CRIMP AREA, ALL OVER 0.002 MIN THICK NICKEL.

3 GOLD FLASH THIS AREA PROVIDED FOR VISUAL INDICATION THAT TERMINAL IS GOLD PLATED.




4 PART LUBRICATED WITH CHEMLUBE 1102

5 FEATURE ON CARRIER STRIP IS RAISED ON GOLD PLATED PRODUCT. FEATURE APPEARS ADJACENT TO EVERY OTHER CONTACT MIN.

6 SEE FIGURE 1 FOR REELING DIRECTION.

7 SEE FIGURE 2 FOR REELING DIRECTION.

8. FOR LEVER ASSISTED CONNECTORS WITH SIDE SLIDE ACTION THE ALLOWABLE WIRE BRUSH LENGTH RANGE IS 0.10-0.70MM.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		0 PLC	±
		1 PLC	±
		2 PLC	±0.20
		3 PLC	±
		4 PLC	±3°
		ANGLES	
		FINISH	
		MATERIAL	
		0.25 THK	
		COPPER ALLOY	SEE TABLE

REELING	LUBRICATION	FINISH	WIRE SIZE	PART NUMBER
7	2	1	22	1326028-8
	1	2	18-20	1326028-7
	2	2	22	1326028-6
	1	18-20	1326028-5	
	2	22	1326028-4	
	18-20	1326028-3		
	2	22	1326028-2	
	18-20	1326028-1		

TE Connectivity

CONTACT, FEMALE, 0.64mm GOLD PLATED

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A200779 C=1326028 -

Customer Drawing

SCALE 10:1 SHEET 1 OF 1 REV C3