


HI2220P171R-10

**UNCONTROLLED
DOCUMENT**

PHYSICAL DIMENSIONS:

A	5.59 [.220]	$\pm$ 0.51 [.020]
B	5.08 [.200]	$\pm$ 0.25 [.010]
C	1.52 [.060]	$\pm$ 0.25 [.010]
D	0.76 [.030]	$\pm$ 0.25 [.010]





ELECTRICAL CHARACTERISTICS:


Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	170	
Minimum	128	
Maximum	213	0.030 4000 mA

NOTES: UNLESS OTHERWISE SPECIFIED

1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 13" REELS, 2,000 PCS/REEL.
2. TERMINATION FINISH IS 100% TIN.
3. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
4. OPERATING TEMPERATURE TEMP: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$ (INCLUDING SELF-HEATING)




LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762 [.030] to this dimension.)

RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
PROJECT/PART NUMBER:				REV	PART TYPE:	DRAWN BY:	
C ADD OPERATING TEMPERATURE UPDATE LAIRD LOGO AND REFLOW CURVE 08/05/13 QU HI2220P171R-10				C	CO-FIRE	TMB	
B	UPDATE COMPANY LOGO ADD ROHS	01/23/08	JRK	DATE:	04/02/04	SCALE:	NTS
A	ORIGINAL DRAFT	04/02/04	TMB	CAD #		SHEET:	2 of 2
REV	DESCRIPTION	DATE	INT	HI2220P171R-10-C			