

Customer Information Sheet

DRAWING No.: M50-3100545R

SHEET 2 OF 2


IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



NOTES:

1. PACKING TO CONFORM TO EIA - 481 STANDARDS.
2. CUMULATIVE TOLERANCE OVER 10 PITCHES = ± 0.20 mm.
3. QUANTITY PER $\varnothing 330$ mm REEL = 900 PIECES.
4. FOR DETAILS OF INDIVIDUAL COMPONENT SEE DRAWING M50-310XX45P

RA	A	25.01.08	----
NAME	ISS.	DATE	C/NOTE
APPROVED:		R.ADDE	
CHECKED:		M.G.PLESTED	
DRAWN:		R.ADDE	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com	HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk	HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg
--	--	--

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ± 1 mm
X.X = ± 0.25 mm
X.XX = ± 0.10 mm
X.XXX = ± 0.01 mm
ANGLES = $\pm 5^\circ$
UNLESS STATED

MATERIAL:

BLACK POLYSTYRENE TAPE

FINISH:

S/AREA: mm²

TITLE: 1.27mm PITCH DIL 2x5 WAY
VERTICAL SMT SOCKET ASSY
TAPE AND REELED

DRAWING NUMBER:

M50-3100545R

SHT
2
OF 2