




MATERIAL :
Housing : Zinc alloy nickel plated
Insert : PA 66 UL94 V0
Mating gasket : sealing IP67:Nitril
 sealing IP68:Silicon
O'ring : nitril
Jam Nut : Aluminium alloy nickel plated


PERFORMANCE CHARACTERISTICS :
 Operating temperature : -40°C up to 105°C
 Insulation resistance : 5000 MΩmin
 Withstanding voltage: 2000 Vrms
 (1500 Vrms for 102w2 and 103w3 layouts)
 Corrosion salt spray : 48 hours (96 hours for specification 01)
 Durability : 500 matings and unmatings
 Sealing in mated conditions : IP67 / IP68 3 bars/30min as per IEC60529
 Sealing in mated conditions : IP69K as per DIN40050
 ROHS compliant

NOTES :

- 1- Contact identification and orientation of connector, refer to:
UT0-CONTACT-L-C01 (Male)
UT0-CONTACT-L-C02 (Female)
- 2- Contact to be ordered separately refer to : UT0 catalog
- 3- Insert arrangements refer to: UT0-DHP-001-C01 (Male)
UT0-DHP-002-C01 (Female)
- 4- This drawing covers p/n termination : -H / -H6 / -H01 / -H601
- 5- Packaging : connector is individually packed in a plastic bag


Part Number (Note 4)	Thread 1 (for information)	Thread 2 (for information)	A ±0.5	B Max (Overall length)		C ±0.2	D ±0.2	Ø E +0.10 -0.02	F +0.40 0	G Max (Panel Tickness)	Torque on nut max (Nm)
				Male	Female						
UT07102W2--H-	11/16-24 UNEF Class 2A	9/16-24 UNEF CLASS 2A	27	34				14.91			6
UT07103W3--H-											
UT07103--H-											
UT07104--H-											
UT071044--H-	7/8-20 UNEF Class 2A	11/16-24 UNEF CLASS 2A	32					18.96			9
UT07124--H-											
UT07128--H-	1" 20 UNEF Class 2A	13/16-20 UNEF CLASS 2A	35	36	33	20.9	9.88	22.14	19.10	3.20	10
UT07142G1--H-											
UT07147--H-											
UT07148--H-											
UT071412--H-											
UT071492--H-				34							
UT071619--H-	1"1/8-18 UNEF Class 2A	15/16-20 UNEF CLASS 2A	38.1					25.32			13
UT071823--H-	1" 1/4-18 UNEF Class 2A	1"1/16-18 UNEF CLASS 2A	41.3					28.49			20
UT072028--H-	1" 3/8-18 UNEF Class 2A	1"3/16-18 UNEF CLASS 2A	46	39	39	26.47	11.46	31.68	24.51	6.40	23
UT072030--H-											
UT072235--H-	1" 1/2-18 UNEF Class 2A	1"5/16-18 UNEF CLASS 2A	49.2	39	39	26.47	11.46	34.85	24.51		25
UT072238--H-											
UT072448--H-	1" 5/8-18 UNEF Class 2A	1"7/16-18 UNEF CLASS 2A	53.4	41	41	28.31	12.30	38.03	25.36		26

UT07	10	2W2	P	W	H6	01
Receptacle UT0 : <i>Type 7</i>						
Shell size :						
Insert arrangement : <i>See Note 1</i>						
Contact : <i>P : Male</i> <i>S : Female</i>						
Insert polarisation: <i>No letter : Standard version</i> <i>W, X, Y, Z : Differents orientation</i>						
Sealing version : <i>H : IP67 version</i> <i>H6 : IP68 version</i>						
Specification : <i>No letter : Standard version</i> <i>01 : Jam nut is black anodized</i>						




PIN (P)


FEMALE CONNECTOR



—SOCKET (S)

A	20/04/2015	_CREATION OF THE DRAWING _Cancel & replace UT07-C01		24021
ISS	DATE	Latest modification - by: COUTY L.		MOD N°
Designed by:		CHANTOISEAU P. Date :21/10/2013	CUSTOMER DRAWING	
TITLE		RECEPTACLE UT0 CONNECTOR		
Scale 2/1		General linear Tolerances: ± 0.1	NPRDS / PROJECT UT0	
SOURIAU		WWW.SOURIAU.COM		This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT A2	SOURIAU DRG N° C001-UT07-A			SHEET 1 / 2

In case the connectors are equipped
with dipsolder contacts




CONTACT RM20M12E84x (Male)
or RC20M12E83x (Female)

Contacts to be ordered separately


MALE CONTACTS		
Part Number	G	
	min	max
UT07104P-H-	11.2	13.5
UT071044P-H-		
UT07128P-H-		
UT071412P-H-		
UT071492P-H-		
UT071619P-H-	7.1	9.2
UT071823P-H-		
UT072028P-H-		
UT072030P-H-		
UT072235P-H-		
UT072238P-H-	5.7	7.8
UT072448P-H-		

FEMALE CONTACTS		
Part Number	G	
	min	max
UT07104S-H-	0.45	2.45
UT071044S-H-		
UT07128S-H-		
UT071412S-H-		
UT071492S-H-		
UT071619S-H-	NOT EXISTING	NOT EXISTING
UT071823S-H-		
UT072028S-H-		
UT072030S-H-		
UT072235S-H-		
UT072238S-H-		
UT072448S-H-		

Panel Cut Out



Part Number (Male or Female)	L	Ø M
UT07102W2--H-	$16.45^{+0.2}_0$	$17.30^{+0.25}_0$
UT07103W3--H-		
UT07103--H-		
UT07104--H-		
UT071044--H-		
UT07124--H-	$20.85^{+0.3}_0$	$22.10^{+0.3}_0$
UT07128--H-		
UT07142G1--H-	$24.00^{+0.3}_0$	$25.40^{+0.3}_0$
UT07147--H-		
UT07148--H-		
UT071412--H-		
UT071492--H-		
UT071619--H-	$27.10^{+0.3}_0$	$28.20^{+0.3}_0$
UT071823--H-	$30.20^{+0.3}_0$	$31.70^{+0.3}_0$
UT072028--H-	$33.40^{+0.3}_0$	$34.70^{+0.3}_0$
UT072030--H-		
UT072235--H-	$36.60^{+0.3}_0$	$37.80^{+0.3}_0$
UT072238--H-		
UT072448--H-	$39.80^{+0.3}_0$	$41.10^{+0.3}_0$

A	20/04/2015	_ CREATION OF THE DRAWING		24021
		_Cancel & replace UT07-C01		
ISS	DATE	Latest modification - by: COUTY L.		MOD N°
Designed by:		CHANTOISEAU P. Date : 21/10/2013		CUSTOMER DRAWING
TITLE		RECEPTACLE UT0 CONNECTOR		
Scale 3/1		General linear Tolerances: ± 0.1	NPRDS / PROJECT UT0	
SOURIAU		WWW.SOURIAU.COM		This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT A2	SOURIAU DRG N° C001-UT07-A			SHEET 2 / 2