

M62382FP

5 V Type 12-bit 4ch Composite Multiplying D/A Converter

REJ03D0882-0300

Rev.3.00

Mar 25, 2008

Description

The M62382FP is a semiconductor integrated circuit of 5 V CMOS structure with 12-bit 4 channels of built-in multiplying D/A converters and 8-bit 8 channels of built-in multiplying D/A converters. 8-bit D/A converters, when used in combination with 12-bit D/A converters, can operate in a wider range. Parallel data input under the 2 modes (A, B) of channel assignment allows for easier usage.

Features

- Built-in low power 12-bit 4 channels D/A converters
- 8-bit D/A converter with buffer making full swing between V_{CC} and GND.
- 2 modes (A, B) of channel assignment
- Zero level function


Built-in function of retaining arbitrary assigned data in 12-bit D/A converter. In normal use, output voltage can be switched to the voltage corresponding to the formerly assigned data by the setting of Z01, making it possible to calibrate the data (output voltage value).

Application


High precision measurement equipments such as memory testers, industrial measurement equipments, medical equipments, standard equipments in general

Not recommended
for new design

Block Diagram



Pin Arrangement



Pin Description

Pin No.	Pin Name	Function
1, 25, 51, 75	VrefL (12)	12-bit D/A converter lower reference voltage input terminal
2, 24, 52, 74	DAout (12)	12-bit D/A converter output terminal
3, 23, 53, 73	VrefU (12)	12-bit D/A converter upper reference voltage input terminal
5, 9, 17, 21, 55, 59, 67, 71	VrefL (8)	8-bit D/A converter lower reference voltage input terminal
6, 10, 16, 20, 56, 60, 66, 70	DAout (8)	8-bit D/A converter output terminal
7, 11, 15, 19, 57, 61, 65, 69	VrefU (8)	8-bit D/A converter upper reference voltage input terminal
27, 49	V _{CC}	Analog power supply terminal
12, 14, 62, 64, 78	GND	Analog GND terminal
47	V _{DD}	Digital power supply terminal
28, 48, 98	V _{SS}	Digital GND terminal
30, 31, 33, 34, 36, 37, 39, 40, 42	A00 to A08	Address terminal
79, 81, 82, 84, 85, 87, 89, 91, 92, 94, 95, 97	D00 to D11	D/A data terminal
43	LD	D/A LD terminal
46	Z00	Zero level data assignment terminal
45	Z01	Zero level data load terminal
4, 8, 13, 18, 22, 29, 32, 35, 38, 41, 44, 50, 54, 58, 63, 68, 72, 76, 77, 80, 83, 86, 88, 90, 93, 96, 99, 100	NC	Non-connection

Absolute Maximum Ratings

Item	Symbol	Ratings	Unit
Digital supply voltage	V _{DD}	-0.3 to +7.0	V
Analog supply voltage	V _{CC}	-0.3 to +7.0	V
Digital input voltage	V _{DIN}	-0.3 to V _{DD} + 0.3 ≤ 7.0	V
D/A reference voltage	V _{ref}	-0.3 to V _{DD} + 0.3 ≤ 7.0	V
D/A output voltage	V _{DAout}	-0.3 to V _{DD} + 0.3 ≤ 7.0	V
Operating temperature	T _{opr}	-20 to +85	°C
Storage temperature	T _{str}	-40 to +125	°C

Electrical Characteristics

<Digital Part>

($V_{DD} = V_{CC} = 5\text{ V}$, $V_{SS} = \text{GND} (= 0\text{ V})$, $V_{refU} = V_{CC}$, $V_{refL} = \text{GND}$, $T_a = -20\text{ to }+85^\circ\text{C}$, unless otherwise noted.)

Item	Symbol	Limits			Unit	Conditions
		Min	Typ	Max		
Digital supply current	I_{DD}	—	—	3.0	mA	$f_{LD} = 1\text{ MHz}$, $V_{DIN} = V_{SS}$, or V_{DD}
Input leak current	I_{ILK}	-10	—	+10	μA	$V_{DIN} = V_{SS}$ to V_{DD}
Input capacitive load	C_{IN}	—	—	1.2	pF	

<Analog Part>

($V_{DD} = V_{CC} = 5\text{ V}$, $V_{SS} = \text{GND} (= 0\text{ V})$, $V_{refU} = V_{CC}$, $V_{refL} = \text{GND}$, $T_a = -20\text{ to }+85^\circ\text{C}$, unless otherwise noted.)


Item	Symbol	Limits			Unit	Conditions	
		Min	Typ	Max			
Analog supply current	I_{CC}	—	1.6	6.0	mA	D/A output = 1/2 MSB	
Reference current for D/A converter (U to L)	I_{ref}	—	0.7	2.0	mA	12-bit D/A	D/A data for maximum current of D/A reference, each circuit current from V_{refU} to V_{refL}
		—	0.1	0.4	mA	8-bit D/A	
Buffer amplifier output drive range	I_{OA}	± 1.5	—	—	mA	Upper side saturation voltage = 0.3 V Lower side saturation voltage = 0.3 V	
Output resistance	R_O	—	2.2	—	k Ω	12-bit D/A: R-2R ladder output	
		—	10	—	Ω	8-bit D/A: Buffer amplifier output	
Differential nonlinearity error	S_{DL}	-1.5	—	+1.5	LSB	12-bit D/A	$V_{refU} = 5.0\text{ V}$, $V_{refL} = 0.0\text{ V}$ $T_a = 25^\circ\text{C}$
		-1.0	—	+1.0		8-bit D/A	
Nonlinearity error	S_{NL}	-2.0	—	+2.0	LSB	12-bit D/A	$V_{refU} = 5.0\text{ V}$, $V_{refL} = 0.0\text{ V}$ $T_a = 25^\circ\text{C}$
		-1.0	—	+1.0		8-bit D/A	
Zero code error	S_{ZERO}	-3.0	—	+3.0	LSB	$V_{refU} = 5.0\text{ V}$, $V_{refL} = 0.0\text{ V}$ $T_a = 25^\circ\text{C}$	
Full code error	S_{FULL}	-3.0	—	+3.0	LSB	$V_{refU} = 5.0\text{ V}$, $V_{refL} = 0.0\text{ V}$ $T_a = 25^\circ\text{C}$	
Temperature coefficient of nonlinearity error	$\Delta\text{NL}/t$	—	—	0.05	LSB/ $^\circ\text{C}$	$V_{refU} = 5.0\text{ V}$, $V_{refL} = 0.0\text{ V}$ $S_{NL\ 12\text{-bit D/A}} / 60^\circ\text{C}$ ($T_a = 25\text{ to }85^\circ\text{C}$)	
Cross talk between the channels	CT	—	75	—	dB	12-bit D/A	$V_{in} = -10\text{ dBm}$ $f = 100\text{ Hz to }1\text{ kHz}$
		—	65	—		8-bit D/A	
Power supply rejection ratio	PSRR	—	65	—	dB	12-bit D/A	$V_{CCin} = V_{CC} - 10\text{ dBm}$ $f = 100\text{ Hz to }1\text{ kHz}$
		—	55	—		8-bit D/A	
Temperature coefficient of D/A output	TCo	—	20	—	ppm/ $^\circ\text{C}$		
Settling time of 12-bit D/A	t_{STDA}	—	1.4	—	μs	Without load ($I_{OA} = 0\text{ mA}$)	
Settling time of 8-bit D/A	t_{stDA}	—	70	—	μs	Until output takes 1/2 LSB of the final value	

Recommended Operating Condition


(Ta = 25 to 75°C)

Item	Symbol	Limits			Unit	Conditions
		Min	Typ	Max		
Analog power supply voltage	V _{CC}	4.5	5.0	5.5	V	
Digital power supply voltage	V _{DD}	4.5	5.0	5.5	V	
H side D/A reference voltage	V _{refH}	V _{CC} - 0.5	—	V _{CC}	V	
L side D/A reference voltage	V _{refL}	GND	—	0.5	V	
H level digital input voltage	V _{IH}	2	—	V _{DD}	V	
L level digital input voltage	V _{IL}	GND	—	0.8	V	
D/A data set up time	t _{DDCH}	10	—	—	ns	Driving 12-bit and 8-bit D/A converters at same time
Address data set up time	t _{ADCH}	150	—	—	ns	Driving 12-bit and 8-bit D/A converters at same time
D/A data hold time	t _{DCHD}	t _{LDH} + 35	—	—	ns	Driving 12-bit and 8-bit D/A converters at same time
Address data hold time	t _{ACHD}	t _{LDH} + 10	—	—	ns	Driving 12-bit and 8-bit D/A converters at same time
Load signal H level hold time	t _{LDH}	100	—	—	ns	Driving 12-bit and 8-bit D/A converters at same time
Z00 signal H level hold time	t _{ZSH}	15	—	—	ns	

Timing Chart



Zero Level Setting (input/output): Z00, Z01



Digital Format

1. Channel Select Setting (A01, A02)

Setting Select	A01	A00
CH1 select	0	0
CH2 select	0	1
CH3 select	1	0
CH4 select	1	1

2. Channel Assign Mode Setting (A02)

Channel Assign Mode Setting	A02
A channel assign mode	0
B channel assign mode	1

3. 8-bit D/A Converter Select Setting (A03)

8-bit D/A Converter Select Setting	A03
D/A select for offset	0
D/A select for gain	1

4. D/A Converter Select Setting (A04)

D/A Converter Select Setting	A04
12-bit D/A converter select	0
8-bit D/A converter select	1

5. Channel Select Setting B (A05, A06, A07, A08)

Setting Select	A05	A06	A07	A08
CH1 select	1	0	0	0
CH2 select	0	1	0	0
CH3 select	0	0	1	0
CH4 select	0	0	0	1


12-bit D/A

D00	D01	D02	D03	D04	D05	D06	D07	D08	D09	D10	D11	D/A Output
0	0	0	0	0	0	0	0	0	0	0	0	V_{refL12}
1	0	0	0	0	0	0	0	0	0	0	0	$(V_{refU12} - V_{refL12}) / 4096 \times 1$
0	1	0	0	0	0	0	0	0	0	0	0	$(V_{refU12} - V_{refL12}) / 4096 \times 2$
1	1	0	0	0	0	0	0	0	0	0	0	$(V_{refU12} - V_{refL12}) / 4096 \times 3$
:	:	:	:	:	:	:	:	:	:	:	:	:
0	0	1	1	1	1	1	1	1	1	1	1	$(V_{refU12} - V_{refL12}) / 4096 \times 4092$
1	0	1	1	1	1	1	1	1	1	1	1	$(V_{refU12} - V_{refL12}) / 4096 \times 4093$
0	1	1	1	1	1	1	1	1	1	1	1	$(V_{refU12} - V_{refL12}) / 4096 \times 4094$
1	1	1	1	1	1	1	1	1	1	1	1	$(V_{refU12} - V_{refL12}) / 4096 \times 4095$


8-bit D/A

D00	D01	D02	D03	D04	D05	D06	D07	D08	D09	D10	D11	D/A Output
0	0	0	0	0	0	0	0	—	—	—	—	VrefL8
1	0	0	0	0	0	0	0	—	—	—	—	$(VrefU8 - VrefL8) / 256 \times 1$
0	1	0	0	0	0	0	0	—	—	—	—	$(VrefU8 - VrefL8) / 256 \times 2$
1	1	0	0	0	0	0	0	—	—	—	—	$(VrefU8 - VrefL8) / 256 \times 3$
:	:	:	:	:	:	:	:	:	:	:	:	:
0	0	1	1	1	1	1	1	—	—	—	—	$(VrefU8 - VrefL8) / 256 \times 252$
1	0	1	1	1	1	1	1	—	—	—	—	$(VrefU8 - VrefL8) / 256 \times 253$
0	1	1	1	1	1	1	1	—	—	—	—	$(VrefU8 - VrefL8) / 256 \times 254$
1	1	1	1	1	1	1	1	—	—	—	—	$(VrefU8 - VrefL8) / 256 \times 255$


8-bit D/A Converter for Reference Voltage Power Supply



Ultra High Precision D/A Converter



Application Circuit



Caution




This IC has four different kinds of terminals, which are to be applied by constant voltage when used. (V_{CC} , V_{DD} , V_{refU} , V_{refL})

D/A converter precision may be worsened when ripple voltage or spike is duplicated on these four terminals.

So please be sure to put capacitor between each terminal and GND for stabilized D/A converter operation.

Package Dimensions

JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-LQFP100-14x14-0.50	PLQP0100KB-A	100P6Q-A / FP-100U / FP-100UV	0.6g



NOTE)
 1. DIMENSIONS **1* AND **2* DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION **3* DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	13.9	14.0	14.1
E	13.9	14.0	14.1
A ₂	—	1.4	—
H _D	15.8	16.0	16.2
H _E	15.8	16.0	16.2
A	—	—	1.7
A ₁	0.05	0.1	0.15
b _p	0.15	0.20	0.25
b ₁	—	0.18	—
c	0.09	0.145	0.20
c ₁	—	0.125	—
θ	0°	—	8°
Ⓜ	—	0.5	—
x	—	—	0.08
y	—	—	0.08
Z _D	—	1.0	—
Z _E	—	1.0	—
L	0.35	0.5	0.65
L ₁	—	1.0	—

Not recommended for new design

Notes:

1. This document is provided for reference purposes only so that Renesas customers may select the appropriate Renesas products for their use. Renesas neither makes warranties or representations with respect to the accuracy or completeness of the information contained in this document nor grants any license to any intellectual property rights or any other rights of Renesas or any third party with respect to the information in this document.
2. Renesas shall have no liability for damages or infringement of any intellectual property or other rights arising out of the use of any information in this document, including, but not limited to, product data, diagrams, charts, programs, algorithms, and application circuit examples.
3. You should not use the products or the technology described in this document for the purpose of military applications such as the development of weapons of mass destruction or for the purpose of any other military use. When exporting the products or technology described herein, you should follow the applicable export control laws and regulations, and procedures required by such laws and regulations.
4. All information included in this document such as product data, diagrams, charts, programs, algorithms, and application circuit examples, is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas products listed in this document, please confirm the latest product information with a Renesas sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas such as that disclosed through our website. (<http://www.renesas.com>)
5. Renesas has used reasonable care in compiling the information included in this document, but Renesas assumes no liability whatsoever for any damages incurred as a result of errors or omissions in the information included in this document.
6. When using or otherwise relying on the information in this document, you should evaluate the information in light of the total system before deciding about the applicability of such information to the intended application. Renesas makes no representations, warranties or guarantees regarding the suitability of its products for any particular application and specifically disclaims any liability arising out of the application and use of the information in this document or Renesas products.
7. With the exception of products specified by Renesas as suitable for automobile applications, Renesas products are not designed, manufactured or tested for applications or otherwise in systems the failure or malfunction of which may cause a direct threat to human life or create a risk of human injury or which require especially high quality and reliability such as safety systems, or equipment or systems for transportation and traffic, healthcare, combustion control, aerospace and aeronautics, nuclear power, or undersea communication transmission. If you are considering the use of our products for such purposes, please contact a Renesas sales office beforehand. Renesas shall have no liability for damages arising out of the uses set forth above.
8. Notwithstanding the preceding paragraph, you should not use Renesas products for the purposes listed below:
 - (1) artificial life support devices or systems
 - (2) surgical implantations
 - (3) healthcare intervention (e.g., excision, administration of medication, etc.)
 - (4) any other purposes that pose a direct threat to human lifeRenesas shall have no liability for damages arising out of the uses set forth in the above and purchasers who elect to use Renesas products in any of the foregoing applications shall indemnify and hold harmless Renesas Technology Corp., its affiliated companies and their officers, directors, and employees against any and all damages arising out of such applications.
9. You should use the products described herein within the range specified by Renesas, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas shall have no liability for malfunctions or damages arising out of the use of Renesas products beyond such specified ranges.
10. Although Renesas endeavors to improve the quality and reliability of its products, IC products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Please be sure to implement safety measures to guard against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other applicable measures. Among others, since the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
11. In case Renesas products listed in this document are detached from the products to which the Renesas products are attached or affixed, the risk of accident such as swallowing by infants and small children is very high. You should implement safety measures so that Renesas products may not be easily detached from your products. Renesas shall have no liability for damages arising out of such detachment.
12. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written approval from Renesas.
13. Please contact a Renesas sales office if you have any questions regarding the information contained in this document, Renesas semiconductor products, or if you have any other inquiries.



RENESAS SALES OFFICES

<http://www.renesas.com>

Refer to "<http://www.renesas.com/en/network>" for the latest and detailed information.

Renesas Technology America, Inc.
450 Holger Way, San Jose, CA 95134-1368, U.S.A
Tel: <1> (408) 382-7500, Fax: <1> (408) 382-7501

Renesas Technology Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: <44> (1628) 585-1000, Fax: <44> (1628) 585-900

Renesas Technology (Shanghai) Co., Ltd.
Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd, Pudong District, Shanghai, China 200120
Tel: <86> (21) 5877-1818, Fax: <86> (21) 6887-7858/7898

Renesas Technology Hong Kong Ltd.
7th Floor, North Tower, World Finance Centre, Harbour City, Canton Road, Tsimshatsui, Kowloon, Hong Kong
Tel: <852> 2265-6688, Fax: <852> 2377-3473

Renesas Technology Taiwan Co., Ltd.
10th Floor, No.99, Fushing North Road, Taipei, Taiwan
Tel: <886> (2) 2715-2888, Fax: <886> (2) 3518-3399

Renesas Technology Singapore Pte. Ltd.
1 Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: <65> 6213-0200, Fax: <65> 6278-8001

Renesas Technology Korea Co., Ltd.
Kukje Center Bldg. 18th Fl., 191, 2-ka, Hangang-ro, Yongsan-ku, Seoul 140-702, Korea
Tel: <82> (2) 796-3115, Fax: <82> (2) 796-2145

Renesas Technology Malaysia Sdn. Bhd
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No.18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: <603> 7955-9390, Fax: <603> 7955-9510