



UBG600-2-1

0.6 m x 1.0 m | 2 ft x 3 ft Grid Antenna for Unlicensed Band, single-polarized, 2.300–2.900 GHz, Type N Female, gray antenna, standard pack—one-piece reflector (pack of 1)

General Specifications

Packing	Standard pack
Reflector Construction	One-piece reflector
Antenna Input	N Female
Antenna Color	Gray
Antenna Type	UB - Directional Antenna for Unlicensed Band, single-polarized
Diameter, nominal	0.6 m x 1.0 m 2 ft x 3 ft
Flash Included	No
Includes	Mounting kit
Package Quantity	1
Polarization	Single

Electrical Specifications

Beamwidth, Horizontal	8.0 °
Beamwidth, Vertical	10.0 °
Cross Polarization Discrimination (XPD)	24 dB
Electrical Compliance	ETSI 301 525 V1.1.1 (2000-06) Class TS 1
Front-to-Back Ratio	32 dB
Gain, Low Band	23.0 dBi
Gain, Mid Band	23.5 dBi
Gain, Top Band	24.0 dBi
Operating Frequency Band	2.300 – 2.900 GHz
Return Loss	11.7 dB
VSWR	1.70

Mechanical Specifications

Fine Elevation Adjustment	±10°
Mounting Pipe Diameter	25 mm–51 mm 1 in–2 in
Net Weight, per unit with mounting kit	4 kg 8 lb
Side Struts, Included	0
Side Struts, Optional	0
Wind Velocity Operational	120 km/h 75 mph
Wind Velocity Survival Rating	160 km/h 99 mph


Wind Forces At Wind Velocity Survival Rating

UBG600-2-1



Angle α for MT Max	5 °
Axial Force (FA)	1078 N 242 lbf
Side Force (FS)	98 N 22 lbf
Twisting Moment (MT)	117 N•m
Weight with 1/2 in (12 mm) Radial Ice	18 kg 40 lb
Zcg with 1/2 in (12 mm) Radial Ice	138 mm 5 in
Zcg without Ice	147 mm 6 in

Wind Forces At Wind Velocity Survival Rating Image



Packed Dimensions


Gross Weight, Packed Antenna	6.0 kg 13.2 lb
Height	460.0 mm 18.1 in
Length	745.0 mm 29.3 in
Volume	255.3 m ³
Width	745.0 mm 29.3 in

UBG600-2-1

POWERED BY



Antenna Dimensions And Mounting Information



Dimensions in Inches (mm)

Antenna Size (mm)	A	B	C	D
2 (51.3)	32.9 (836.7)	21.4 (542.8)	3.5 (89)	3.7 (93.2)

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2008

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system



* Footnotes

Axial Force (FA)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Cross Polarization Discrimination (XPD)	The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.
Front-to-Back Ratio	Denotes highest radiation relative to the main beam, at $180^\circ \pm 40^\circ$, across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.
Gain, Mid Band	For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.
Operating Frequency Band	Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.
Packing	Andrew standard packing is suitable for export. Antennas are shipped as

UBG600-2-1

POWERED BY



standard in totally recyclable cardboard or wire-bound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.

Return Loss

The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.

Side Force (FS)

Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Twisting Moment (MT)

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

VSWR

Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.

Wind Velocity Operational

The wind speed where the antenna deflection is equal to or less than 0.1 degrees. In the case of ValuLine antennas, it is defined as a maximum deflection of 0.3 x the 3 dB beam width of the antenna.

Wind Velocity Survival Rating

The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.